



The *only* patch panel that allows installers to utilize a multi-pair termination tool while terminating with one hand!

To support faster deployment in enterprise networks, REVConnect Patch Panels are based on innovative REVConnect termination technology, designed with time-saving features for installers and end-users. The patch panels can be terminated from the rear or front. Removable 6-port modules with a unique cable-measuring feature keeps cables organized during the termination process and improves cable management. Patch panels can be identified using labels or icons.



### BENEFITS

- Simplifies project logistics with one termination method for patch panels and workstations
- Easy project planning and material ordering with one part number
- Efficient assembly in live equipment cabinets and wall-mount racks
- Easy maintenance and guaranteed 100% port availability
- No extra accessories needed for tidy cable management
- Labeling material complies with ANSI/TIA-606



### FEATURES

- Preloaded Panels are fully assembled with 24 or 48 jack housings and REVConnect cores
- Single-port modularity using standard REVConnect jacks
- Cable management bar included (one for 24-port, two for 48-port)
- Pre-printed ID card and labeling window for port identification
- Label sheets (sold separately - AX107527) can be printed using LabelFlex software (optional)
- Available in Category 5e, 6 and 6A, standard black or white (for low-light environments), and flat or angled configurations



For more information, visit  
[www.belden.com/revconnect](http://www.belden.com/revconnect)  
or call **1.800.BELDEN.1**

## ORDERING INFORMATION

### REVConnect Preloaded Patch Panels

Description	Belden Part Number	
	Black Panels	White Panels
<b>Category 6A</b>		
10GX REVConnect Patch Panel 24-port, 1U (Preloaded)	RVAPPF1U24BK	RVAPPF1U24WH
10GX REVConnect Patch Panel 48-port, 2U (Preloaded)	RVAPPF2U48BK	RVAPPF2U48WH
10GX REVConnect Angled Patch Panel 24-port, 1U (Preloaded)	RVAPPA1U24BK	RVAPPA1U24WH
10GX REVConnect Angled Patch Panel 48-port, 2U (Preloaded)	RVAPPA2U48BK	RVAPPA2U48WH
<b>Category 6</b>		
CAT6+ REVConnect Patch Panel 24-port, 1U (Preloaded)	RV6PPF1U24BK	RV6PPF1U24WH
CAT6+ REVConnect Patch Panel 48-port, 2U (Preloaded)	RV6PPF2U48BK	RV6PPF2U48WH
CAT6+ REVConnect Angled Patch Panel 24-port, 1U (Preloaded)	RV6PPA1U24BK	RV6PPA1U24WH
CAT6+ REVConnect Angled Patch Panel 48-port, 2U (Preloaded)	RV6PPA2U48BK	RV6PPA2U48WH
<b>Category 5e</b>		
CAT5E REVConnect Patch Panel 24-port, 1U (Preloaded)	RV5PPF1U24BK	RV5PPF1U24WH
CAT5E REVConnect Patch Panel 48-port, 2U (Preloaded)	RV5PPF2U48BK	RV5PPF2U48WH
CAT5E REVConnect Angled Patch Panel 24-port, 1U (Preloaded)	RV5PPA1U24BK	RV5PPA1U24WH
CAT5E REVConnect Angled Patch Panel 48-port, 2U (Preloaded)	RV5PPA2U48BK	RV5PPA2U48WH

### REVConnect Modular Patch Panels (Empty)

Description	Belden Part Number	
	Black Panels	White Panels
REVConnect Modular Patch Panel 24-port, 1U (Empty)	RVMPPF1U24BK	RVMPPF1U24WH
REVConnect Modular Patch Panel 48-port, 2U (Empty)	RVMPPF2U48BK	RVMPPF2U48WH
REVConnect Angled Modular Patch Panel 24-port, 1U (Empty)	RVMPPA1U24BK	RVMPPA1U24WH
REVConnect Angled Modular Patch Panel 48-port, 2U (Empty)	RVMPPA2U48BK	RVMPPA2U48WH

### Accessories

Description	Belden Part Number
<b>Labeling</b>	
LabelFlex Labels for REVConnect Patch Panels (64 labels/sheet, 10 sheets/pack)	AX107527
REVConnect Color Icon, Color, Bulk Pack	RVUICxx-B24*
REVConnect Dust Cover, Color, Bulk Pack	RVUDCxx-B24*
<b>Replacement Items</b>	
REVConnect Patch Panel ID Window Replacement Kit (8 Windows + ID Card)	RVUPPID
10GX REVConnect UTP Modular Jack, Black, T568 A/B, Single Pack	RVAMJKUBK-S1
CAT6+ REVConnect UTP Modular Jack, Black, T568 A/B, Single Pack	RV6MJKUBK-S1
CAT5E REVConnect UTP Modular Jack, Black, T568 A/B, Single Pack	RV5MJKUBK-S1
Bulk Pack of REVConnect Cores (included with every panel)	RVUCOEW-B50
<b>REVConnect Tool</b>	
Universal Termination Tool	RVUTT01
Tool Spare Blade Set	RVUTB01
Cable Prep Tool	RVUCT01
Replacement Tool Belt Clip	RVUTC01

\*Replace xx by REVConnect color-code (see table to the right).

### Color-Code Icons and Dust Covers

Description	Color-Code	Belden Part Number	
		Icons	Dust Covers
Gray	GY	RVUICGY-B24	RVUDCGY-B24
Almond	AL	RVUICAL-B24	RVUDCAL-B24
Electrical White	EW	RVUICEW-B24	RVUDCEW-B24
Black	BK	RVUICBK-B24	RVUDCBK-B24
Ivory	IV	RVUICIV-B24	RVUDCIV-B24
Orange	OR	RVUICOR-B24	RVUDCOR-B24
Red	RD	RVUICRD-B24	RVUDCRD-B24
Yellow	YL	RVUICYL-B24	RVUDCYL-B24
Green	GN	RVUICGN-B24	RVUDCGN-B24
Blue	BL	RVUICBL-B24	RVUDCBL-B24
Purple	PR	RVUICPR-B24	RVUDCPR-B24
Brown	BR	RVUICBR-B24	RVUDCBR-B24
Orange, TIA 606	TO	RVUICTO-B24	RVUDCTO-B24
Red, TIA 606	TR	RVUICTR-B24	RVUDCTR-B24
Yellow, TIA 606	TY	RVUICTY-B24	RVUDCTY-B24
Green, TIA 606	TG	RVUICTG-B24	RVUDCTG-B24
Blue, TIA 606	TB	RVUICTB-B24	RVUDCTB-B24
Purple, TIA 606	TP	RVUICTP-B24	RVUDCTP-B24
Brown, TIA 606	TN	RVUICTN-B24	RVUDCTN-B24

© Copyright 2019, Belden Inc.  
REVConnect Preloaded Patch Panels\_V2\_PB00129\_ECOS\_BDC\_0419\_A\_AG