

Product ID Produkt ID	Product Description Produktbezeichnung
136	RKWT 4-251/30 M
137	RKWT 4-225/0,5 M
234	RSWT 4-225/20 M
246	RKWT 4-602/20 M
303	RKT 4-3-294/2 M
304	RKT 4-3-294/10 M
368	RKT 4-225/60 M
393	RKT 4-295/2 M
421	RKT 4-225/45 M
585	RKTS 4-182/20 M
693	RST 4-500/2 M
699	RKT 4-500/2 M
700	RKT 4-500/5 M
701	RKT 4-500/10 M
722	RSWT 4-500/2 M
730	RKWT 4-500/2 M
731	RKWT 4-500/5 M
790	RSWT 4-225/3 M
989	PRST 4-07/15 M
1140	RST 3-534/1,6 M
1245	RKT 4-3-06/20 M
1246	RKT 4-3-06/30 M
1907	RKTS 4-288/35 M
1958	RKTSN 4-182/50 M
2471	RKT 4-3-224/0,6 M
2482	RKWTS 4-288/3 M
2527	RST 4-251/20 M
2544	RKWT 4-3-224/30 M
2574	RST 4-265/7 M
2762	RKWTS 4-288/120 M
3106	RKWT 4U-07/5 M
3148	RST 3-294/5 M
3346	RST 4-295/2 M
3381	RST 4-251/15 M
3797	RKT 4-07/8 M
4256	RKWT 4-295/10 M
4263	RST 4-295/12 M
4311	RST 4-295/1 M
4412	RKT 4-07/6 M
4429	RKTS 4-288/1,5 M
4540	RST 4-295/5 M
4543	RKT 4-295/7 M
4651	RKWT 4-225/12 M
4720	RKWTSN 4-182/6 M
4721	RKWTSN 4-182/8 M
4951	RKTS 4-182/40 M
4952	RKTS 4-182/50 M

Product ID Produkt ID	Product Description Produktbezeichnung
4995	RKWT 4-225/0,6 M
5237	RKT 4-602/30 M
5275	RKWTSN 4-182/15 M
5279	RKT 4-225/0,6 M
5528	RKTS 4-288/0,3 M
5529	RKTS 4-288/0,5 M
5595	RKWTS 4-288/40 M
5677	RSTS 4-288/5,5 M
5707	RKWTSN 4-182/25 M
5722	RSWTS 4-288/5 M
5757	RKT 4-251/30 M
5885	RKT 4U-07/5 M
5977	RKT 4-225/50 M
5983	RKWTSN 4-571/25 M
5984	RKWTSN 4-571/8 M
5985	RKWTSN 4-571/6 M
5986	RKWTSN 4-571/10 M
6337	RKT 4-295/15 M
6778	RKWTS 4-288/35 M
6813	RSWT 4-225/1,1 M
7277	RKT 4-251/3 M
7278	RKT 4-251/1,5 M
7279	RKT 4-251/0,6 M
7350	RKWTSN 4-579/25 M
7351	RKWTSN 4-579/8 M
7352	RKWTSN 4-579/6 M
7353	RKWTSN 4-579/10 M
7907	RKWT 4-295/5 M
7975	RKT 4-225/1,5 M
8067	RKWT 4-225/1,1 M
8124	PRKWT 4-07/8 M
8129	RKWTS 4-288/25 M
8160	RKWT 4-637/5 M
8161	RKWT 4-637/10 M
8264	RKTS 4-288/7,5 M
8349	RKWT 4-3-264/6 M
8354	RKWT 4-265/5 M
8725	RKWTS 4-288/1 M
8752	RKT 4-637/5 M
8771	RKWTS 4-288/50 M
8873	RKWTSN 4-182/5 M
8923	RST 4-07/3 M
9078	RKT 4-637/10 M
9180	RKWT 4-3-294/2 M
9276	RKWTS 4-288/60 M
9424	RKWTS 4-288/100 M
9671	RKT 4-3-224/3,2 M

Product ID Produkt ID	Product Description Produktbezeichnung
10196	RKWTSN 4-182/50 M
10215	RKTSN 4-182/15 M
10519	RKT 3U-226/25 M
10539	RKT 4-637/20 M
10540	RKT 4-637/15 M
10607	RST 4-637/5 M
10713	RKWT 4-637/15 M
10783	RST 4-637/10 M
10837	RKT 3U-12-19/3 M
10998	RKWT 4-288/15 M
11342	RKT 3U-12-19/2 M
11343	RKT 3U-12-19/5 M
11344	RKT 3U-18/10 M
11345	RKT 3U-18/2 M
11346	RKT 3U-18/5 M
11347	RKT 4-07/10 M
11348	RKT 4-07/2 M
11349	RKT 4-07/5 M
11355	RKT 4-225/2 M
11356	RKT 4-225/5 M
11357	RKT 4-251/2 M
11358	RKT 4-251/5 M
11362	RKT 4-3-06/10 M
11363	RKT 4-3-06/2 M
11364	RKT 4-3-06/5 M
11383	RKWT 4-2-63/5 M
11410	RKTS 4-182/10 M
11411	RKTS 4-182/2 M
11412	RKTS 4-182/5 M
11429	RKT 4-3-06/3 M
11430	RKWT 3U-12-19/2 M
11431	RKWT 3U-12-19/5 M
11432	RKWT 3U-18/10 M
11433	RKWT 3U-18/2 M
11434	RKWT 3U-18/5 M
11435	RKWT 4-07/10 M
11436	RKWT 4-07/2 M
11437	RKWT 4-07/5 M
11441	RKWT 4-225/2 M
11442	RKWT 4-225/5 M
11443	RKWT 4-251/2 M
11444	RKWT 4-251/5 M
11445	RKWT 4-29/10 M
11446	RKWT 4-29/2 M
11447	RKWT 4-29/5 M
11448	RKWT 4-3-06/10 M
11449	RKWT 4-3-06/2 M

Product ID Produkt ID	Product Description Produktbezeichnung
11450	RKWT 4-3-06/5 M
11718	RST 3-06/10 M
11719	RST 3-06/2 M
11720	RST 3-06/5 M
11803	RST 4-07/10 M
11804	RST 4-07/2 M
11805	RST 4-07/5 M
11809	RST 4-225/2 M
11810	RST 4-225/5 M
11811	RST 4-251/2 M
11812	RST 4-251/5 M
11899	RKWT 3U-226/20 M
12086	RSTS 4-182/10 M
12087	RSTS 4-182/2 M
12088	RSTS 4-182/5 M
12106	RSWT 3-06/2 M
12112	RSWT 4-07/2 M
12113	RSWT 4-07/5 M
13153	RST 4-637/15 M
13276	RKT 4-07/20 M
13287	PRKT 4-07/10 M
13289	RKT 4-07/15 M
13525	RKWTS 4-288/150 M
13538	RKT 4-798/2 M
13583	RKWT 4-07/15 M
13584	PRKWT 4-07/10 M
13601	PRKWT 4-07/5 M
13602	RKWT 4-29/15 M
13605	RKWT 4-07/20 M
13645	RKWT 4-798/5 M
13662	RKWT 4-798/4 M
13671	RSWTS 4-288/0,05 M
13684	WRST 4-521/0,05 M
13694	PRST 4-07/0,05 M
14319	RST 4-602/3 M
14343	RKWT 4-251/3 M
14547	RKWT 4-132/10 M
14569	RKWT 4-3-06/15 M
14676	RKWT 4-637/2 M
14708	RST 4-29/0,85 M
14743	RKT 4-265/25 M
14820	RST 4-86/0,85 M
14911	RKWTS 4-288/45 M
15243	RKT 4-96/2 M
15569	RKT 4-3-224/1,5 M
15570	RKT 4-132/10 M
15642	PRST 4-07/0,5 M

Product ID Produkt ID	Product Description Produktbezeichnung
15728	RKT 4-3-224/15 M
15729	RKT 4-3-224/10 M
15730	RKT 4-3-224/5 M
15736	RKT 4-3-224/3 M
15737	RKT 4-3-224/25 M
15817	RST 3U P36
15908	RKWTS 4-288/70 M
15933	RKWTS 4-288/110 M
15958	RKWT 4-602/10 M
16058	RKTN 4-225/0,3 M
16059	RKTN 4-225/3 M
16060	RKTN 4-225/1,5 M
16068	RSTN 4-225/1,5 M
16438	RKT 4-340/2 M
16564	RKWTN 4-225/0,3 M
16962	RKT 4-295/2,5 M
17582	RKWTS 4-288/180 M
17773	RKWT 4-07/25 M
18028	PRKWT 4-07/25 M
18031	PRKT 4-07/25 M
18158	RKWT 4-225/10 M
18170	RKT 4-3-224/2 M
18222	RKT 4-225/10 M
18230	PRST 4-07/10 M
18341	RKWTS 4-288/125 M
18917	RKT 4-3-06/3,3 M
20033	RKT 4S-703/1 M
20570	RST 4-225/0,21 M
20823	RKWTS 4-288/200 M
20899	RKT 4-3-294/3 M
21637	RKTS 4-288/12 M
21638	RKTS 4-288/18 M
22114	RSTS 4-288/30 M
22603	RKWT 4-340/2 M
22713	RKWT 4-225/60 M
22714	RKWT 4-225/35 M
23038	RKWT 4-981/0,3 M
23039	RKWT 4-981/0,6 M
23040	RKWT 4-981/1 M
23051	RKWT 4-981/1,5 M
23052	RKWT 4-981/2 M
23053	RKWT 4-981/2,5 M
23054	RKWT 4-981/3 M
23055	RKWT 4-981/3,5 M
23056	RKWT 4-981/4 M
23057	RKWT 4-981/4,5 M
23058	RKWT 4-981/5 M

Product ID Produkt ID	Product Description Produktbezeichnung
23059	RKT 4-981/0,3 M
23060	RKT 4-981/0,6 M
23061	RKT 4-981/1 M
23062	RKT 4-981/1,5 M
23063	RKT 4-981/2 M
23064	RKT 4-981/2,5 M
23065	RKT 4-981/3 M
23066	RKT 4-981/3,5 M
23067	RKT 4-981/4 M
23068	RKT 4-981/4,5 M
23069	RKT 4-981/5 M
23091	RKWT 4-3-980/0,3 M
23093	RKWT 4-3-980/0,6 M
23094	RKWT 4-3-980/1 M
23095	RKWT 4-3-980/1,5 M
23096	RKWT 4-3-980/2 M
23098	RKWT 4-3-980/2,5 M
23099	RKWT 4-3-980/3 M
23100	RKWT 4-3-980/3,5 M
23101	RKWT 4-3-980/4 M
23102	RKWT 4-3-980/4,5 M
23103	RKWT 4-3-980/5 M
23122	RST 4-225/4,5 M
23123	RST 4-225/3,5 M
23124	RST 4-225/0,6 M
23125	RKT 4-3-224/4,5 M
23126	RKT 4-3-224/3,5 M
23127	RKT 4-3-224/0,3 M
23131	RKT 4-3-980/0,3 M
23132	RKT 4-3-980/0,6 M
23133	RKT 4-3-980/1 M
23134	RKT 4-3-980/1,5 M
23135	RKT 4-3-980/2 M
23136	RKT 4-3-980/2,5 M
23137	RKT 4-3-980/3 M
23138	RKT 4-3-980/3,5 M
23139	RKT 4-3-980/4 M
23140	RKT 4-3-980/4,5 M
23141	RKT 4-3-980/5 M
23142	RST 3-980/0,3 M
23143	RST 3-980/0,6 M
23144	RST 3-980/1 M
23145	RST 3-980/1,5 M
23146	RST 3-980/2 M
23147	RST 3-980/2,5 M
23148	RST 3-980/3 M
23149	RST 3-980/3,5 M

Product ID Produkt ID	Product Description Produktbezeichnung
23150	RST 3-980/4 M
23151	RST 3-980/4,5 M
23152	RST 3-980/5 M
23177	RST 4-981/0,3 M
23178	RST 4-981/0,6 M
23179	RST 4-981/1 M
23180	RST 4-981/1,5 M
23181	RST 4-981/2 M
23182	RST 4-981/2,5 M
23183	RST 4-981/3 M
23184	RST 4-981/3,5 M
23185	RST 4-981/4 M
23186	RST 4-981/4,5 M
23187	RST 4-981/5 M
24553	RKTS 4-182/15 M
24857	RKWT 4-07/30 M
25703	RKT 4-251/10 M
26409	RKWT 4-225/15 M
26647	RKWT 4-798/10 M
26875	RST 4-602/5 M
27094	RKWT 4-251/10 M
28336	PRKT 4-07/5 M
29165	RKWT 4-3-224/10 M
29618	RST 4-225/10 M
30309	RST 4-07/20 M
38298	PRST 4-07/2 M
38482	PRKWT 4-07/20 M
39500	RKT 4-602/10 M
39721	RKWT 4-602/5 M
40182	RST 4-07/0,6 M
41731	RST 3-260/2 M
41806	RKT 4-07/3 M
42175	RST 4-225/20 M
42646	RKWT 4-602/2 M
43595	RKWT 4-3-224/2 M
43597	RKWT 4-3-224/5 M
43702	RST 3-224/10 M
43703	RST 3-224/2 M
43704	RST 3-224/5 M
43745	RKT 4-225/7,5 M
44026	RKWTN 4-225/10 M
44079	RST 4-225/0,85 M
44106	RKT 4-225/20 M
44229	RKT 4-225/15 M
44311	RST 3-224/3 M
44317	RKWT 4-3-224/15 M
44407	RKT 4-225/25 M

Product ID Produkt ID	Product Description Produktbezeichnung
44597	RSWT 4-225/5 M
44836	RKT 4-602/5 M
44966	RST 4-225/1 M
45561	RKT 4-07/30 M
45772	RST 4-225/15 M
46274	RKT 4-3-224/1 M
46365	RKT 4-225/30 M
46376	RKWT 4-225/20 M
46377	RKWT 4-225/30 M
46523	RSWT 4-225/2 M
46615	RST 4-602/2 M
46629	RSWT 4-225/10 M
46896	PRST 4-07/25 M
46902	RST 4-251/10 M
47610	RST 3-224/20 M
48136	RKWT 4-225/25 M
48675	RST 4-225/30 M
49145	RKT 4-07/25 M
49202	RKTS 4-288/10 M
49203	RKTS 4-288/2 M
49205	RKTS 4-288/5 M
49306	RSTS 4-288/10 M
49307	RSTS 4-288/2 M
49308	RSTS 4-288/5 M
49314	RKTS 4-288/15 M
49378	RKWT 4-288/5 M
49379	RKWT 4-288/10 M
49743	RKT 4-265/6 M
49985	RST 4-225/3 M
51159	RST 4-07/1 M
51548	RKWT 4-3-224/20 M
51824	RKWT 4-3-224/3 M
51939	RST 4-265/5 M
51974	RKTN 4-225/5 M
51975	RKTN 4-225/10 M
51986	RKTN 4-225/25 M
52025	RKWTN 4-225/5 M
52174	RST 4-07/15 M
52276	RKT 4-3-224/4 M
52386	RKT 4-602/2 M
52412	RKWT 4-225/8 M
53259	PRKT 4-07/2 M
53261	PRKT 4-07/15 M
53263	PRKWT 4-07/2 M
53265	PRKWT 4-07/15 M
53267	RKTN 4-225/15 M
53268	RKWTN 4-225/2 M

Product ID Produkt ID	Product Description Produktbezeichnung
53269	RKWTN 4-225/15 M
53582	RKT 4-265/2 M
54204	RKT 3U-226/5 M
54921	RST 3U-226/5 M
55304	RST 4-602/10 M
56596	RKT 4-288/5 M
57147	RKWT 4-07/50 M
58107	RKWT 4-3-294/5 M
58405	RSTS 4-182/15 M
58734	RKT 4-265/5 M
59202	PRST 4-07/5 M
59368	RST 4 P4
59595	RST 4 P5 22528712
59755	RSTS 4-288/0,3 M
60053	RKT 4-3-224/20 M
60074	RKWTN 4-225/1 M
60075	RKWT 4-225/1 M
60434	RKTS 4-288/20 M
60987	RKT 4-07/40 M
60988	RKWT 4-07/40 M
62725	PRKWT 4-07/60 M
62746	PRKWT 4-07/40 M
63650	RST 4-225/0,3 M
64219	RKWT 4-225/3 M
64235	RKT 4-07/0,5 M
65558	PRKT 4-07/50 M
65588	RST 3-224/1 M
65638	RKWT 4-251/15 M
65773	RKTS 4-288/30 M
65828	RKTS 4-288/25 M
66775	RKWT 4-3-06/20 M
69550	PRKWT 4-07/50 M
70574	RKT 4-288/10 M
71255	RST 3-260/5 M
71266	RST 3-260/10 M
71267	RKT 4-3-260/2 M
71268	RKT 4-3-260/5 M
71269	RKT 4-3-260/10 M
71290	RKWT 4-3-260/2 M
71291	RKWT 4-3-260/5 M
71292	RKWT 4-3-260/10 M
71568	RST 3-224/1,5 M
72487	RSTS 4-288/3 M
74744	RKWTN 3U-226/10 M
74892	RKT 4-602/15 M
75520	PRKT 4-07/20 M
75944	PRST 4-07/0,3 M

Product ID Produkt ID	Product Description Produktbezeichnung
76347	RKT 3U-226/10 M
76494	RKT 4-295/5 M
76495	RKT 4-295/10 M
78858	RKWT 4-288/2 M
79047	RKT 4-251/15 M
79199	RKT 4-225/0,3 M
79541	RKT 4-225/3 M
79769	RKWT 4-07/0,5 M
80489	RKWT 3U-226/2 M
81115	RST 4-225/7,5 M
81531	RKWT 4-07/1 M
81946	RKT 4-225/1 M
81994	RST 4-265/10 M
82860	RKT 4-265/4 M
83175	RKWT 4-3-06/30 M
84086	RKWT 4-288/30 M
84713	RKT 4-07/1 M
84956	RST 4 P6
86054	RKWT 4-288/20 M
86075	RKWT 3U-12-19/10 M
86982	PRKT 4-07/35 M
87355	RSWT 4-225/1 M
87382	RKWT 3U-226/5 M
88351	RKT 4-265/10 M
90512	RST 4-225/25 M
91183	RKT 3U-226/2 M
91332	RST 4-265/2 M
92031	RKTS 4-288/6 M
93660	RKWT 4-34/1,5 M
93683	RKWT 4-225/6 M
93741	RST 4-602/20 M
94177	RKWT 4-3-224/1 M
98377	RST 4-225/1,7 M
98787	RSTN 4-225/1 M
99620	RSTS 4-288/6 M
103195	RKTS 4-288/3 M
103683	RKT 4-602/1 M
103684	RKT 4-602/3 M
103981	RST 4-225/6 M
104372	RKT 4-602/4 M
104498	RKT 4-602/20 M
105024	RKT 4-265/15 M
105225	RST 4-251/3 M
107039	RKWTN 4-251/10 M
107230	RKTSN 4-182/5 M
107231	RKTSN 4-182/10 M
107774	RKT 4-251/20 M

Product ID Produkt ID	Product Description Produktbezeichnung
107968	RKWT 4-29/25 M
108051	RST 4-225/8,5 M
108265	RKT 4-3-224/6 M
108335	RKTSN 4-182/25 M
108363	RKT 4-3-224/0,5 M
108632	RKT 4-265/2,5 M
108806	RKT 4-251/7,5 M
109338	RKT 4-265/3 M
109339	RKWT 4-265/3 M
934636022	RKT 4-225/8 M
934636024	RKT 4-225/11 M
934636102	RSWT 4-225/6 M
934636114	RKWT 4-225/50 M
934636133	RSWT 3-224/2 M
934636259	RST 3-224/15 M
934636520	RKT 4-295/3 M
934636540	RST 4-225/4 M
934636544	RKT 4-225/4 M
934636547	RKT 4-225/0,5 M
934636641	RST 4U-07/5 M
934636686	RKWT 4-265/10 M
934636791	RSTS 4-288/1M
934636888	RSTS 4-288/20 M
934636936	RKTS 4-288/1 M
934637060	PRKT 4-07/40 M
934637108	RKTS 4-288/50 M
934637147	PRST 4-96/5 M
934637227	RKTS 4-182/3 M
934637228	RSTS 4-182/3 M
934637296	RKT 4-3-224/2,5 M
934637377	RKT 4-251/2,5 M
934637422	RST 4-265/20 M
934637472	RST 4-225/2,5 M
934637548	RKWT 4-225/40 M
934637550	RKT 4-225/40 M
934637552	RKTS 4-288/40 M
934637704	RST 4-225/1,5 M
934637754	RKWT 4-251/7 M
934637760	RKWT 4-225/7 M
934703001	RKWTS 4-182/1 M
934703002	RKWTS 4-182/10 M
934703003	RKWTS 4-182/15 M
934703004	RKWTS 4-182/2 M
934703005	RKWTS 4-182/20 M
934703006	RKWTS 4-182/25 M
934703007	RKWTS 4-182/5 M
934703009	RKWTS 4-288/10 M

Product ID Produkt ID	Product Description Produktbezeichnung
934703010	RKWTS 4-288/15 M
934703011	RKWTS 4-288/2 M
934703012	RKWTS 4-288/20 M
934703013	RKWTS 4-288/30 M
934703014	RKWTS 4-288/5 M
934703015	RKWTS 4-288/6 M
934703033	RKWTSN 4-182/10 M
934704001	RSWTS 4-288/0,52 M
934704002	RSWTS 4-288/0,55 M
934733001	WRKT 4-3-520/2 M
934733002	WRKT 4-3-520/5 M
934733003	WRKT 4-3-520/10 M
934733004	WRKT 4-3-520/15 M
934733005	WRKT 4-3-520/20 M
934733006	WRKT 4-3-520/25 M
934733007	WRKT 4-521/2 M
934733008	WRKT 4-521/5 M
934733009	WRKT 4-521/10 M
934733010	WRKT 4-521/15 M
934733011	WRKT 4-521/20 M
934733012	WRKT 4-521/25 M
934734001	WRKWT 4-3-520/2 M
934734002	WRKWT 4-3-520/5 M
934734003	WRKWT 4-3-520/10 M
934734004	WRKWT 4-3-520/15 M
934734005	WRKWT 4-3-520/20 M
934734006	WRKWT 4-3-520/25 M
934734007	WRKWT 4-521/2 M
934734008	WRKWT 4-521/5 M
934734009	WRKWT 4-521/10 M
934734010	WRKWT 4-521/15 M
934734011	WRKWT 4-521/20 M
934734012	WRKWT 4-521/25 M
934735001	WRST 3-520/2 M
934735002	WRST 3-520/5 M
934735007	WRST 4-521/2 M
934735008	WRST 4-521/5 M
934735009	WRST 4-521/10 M
934735010	WRST 4-521/15 M
934735012	WRST 4-521/25 M
934736001	WRSWT 3-520/2 M
934736002	WRSWT 3-520/5 M
934736007	WRSWT 4-521/2 M
934736008	WRSWT 4-521/5 M
934736009	WRSWT 4-521/10 M
934736012	WRSWT 4-521/25 M