



A unique patch panel offering a cost-effective, high-performance solution for zone cabling

To support faster deployment in enterprise networks, REVConnect Coupler Patch Panels are based on innovative REVConnect termination technology, designed with time-saving features for installers and end-users. The patch panels can be terminated from the rear or front. Removable six-port modules provide front access termination and have a unique cable-measuring feature that keeps cables organized and improves cable management.



BENEFITS

- Reduce costs and inventory by reusing leftover shorts to create core-to-core assemblies in place of patch cords for cut-to-length patching
- Simplify logistics with one termination method for patch panels and workstations
- Easy project planning and material ordering with one part number
- Efficient assembly in live equipment cabinets and wall-mount racks
- No extra accessories needed for tidy cable management
- Complies with ANSI/TIA-606



FEATURES

- User interface uses REVConnect receptacles
- Fully assembled with REVConnect Couplers that are ready to terminate
- Single-port modularity ensures quick, cost-effective repair if a connection goes bad
- Cable management bar(s) included
- Pre-printed ID card and labeling window for port identification
- Label sheets (sold separately - AX107527) can be printed using LabelFlex software (optional)
- Category 6A flat configuration: choose between 24-port 1U or 48-port 2U



KEY APPLICATIONS

- Applications without RJ45 interfaces
- Consolidation points
- High-density interconnects and cross connects



ORDERING INFORMATION

REVConnect Coupler Patch Panels

| Description | Belden Part Number |
|---|---------------------|
| | Black Panels |
| Category 6A | |
| 10GX REVConnect Coupler Patch Panel 24-port, 1U | RVACPF1U24BK |
| 10GX REVConnect Coupler Patch Panel 48-port, 2U | RVACPF2U48BK |

Accessories

| Description | Belden Part Number |
|--|---------------------|
| Labeling | |
| LabelFlex Labels for REVConnect Patch Panels (64 labels/sheet, 10 sheets/pack) | AX107527 |
| Replacement Items | |
| REVConnect Patch Panel ID Window Replacement Kit (8 Windows + ID Card) | RVUPPID |
| 10GX REVConnect Coupler Black 568A/B (includes 1 core) | RVACPKUBK-S1 |
| Bulk Pack of REVConnect Cores (included with every panel) | RVUCOEW-B50 |
| REVConnect Tool | |
| Universal Termination Tool | RVUTT01 |
| Tool Spare Blade Set | RVUTB01 |
| Cable Prep Tool | RVUCT01 |
| Replacement Tool Belt Clip | RVUTC01 |

For more information, visit
www.belden.com/revconnect
or call **1.800.BELDEN.1**