




Product information OVKS 2,2

Fiber Interfaces:Assimilable LWL components:OptoQuick components:OVKS 2,2

<https://www.e-catalog.beldensolutions.com:443/link/57078-57141-57136-24571-38339/en/conf/ui/state>

| | |
|--|--|
| Name | OVKS 2,2 |
| |  |
| | fiber optic plug;for plastic fiber with an external diameter of 2.2 mm,strain relief 40 N |
| Delivery informations | |
| Availability | available |
| Product description | |
| Description | fiber optic plug; for plastic fiber with an external diameter of 2.2 mm, strain relief 40 N |
| Construction type | OVK OptoQuick |
| Colour | black |
| Type | OVKS 2,2 |
| Order No. | 936 200-001 |
| Scope of delivery and accessories | |
| Scope of delivery | 20 fiber optic plugs, each consisting of a plug body and a strain relief 1 polishing tool 1 operating instructions |

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.