




Product information OVKS 2,2

Fiber Interfaces:Assimilable LWL components:OptoQuick components:OVKS 2,2

<https://www.e-catalog.beldensolutions.com:443/link/57078-57141-57136-24571-38340/en/conf/ui/state>

Name	OVKS 2,2
	
	fiber optic plug;for plastic fiber with an external diameter of 2.2 mm,strain relief 40 N
Delivery informations	
Availability	available
Product description	
Description	fiber optic plug; for plastic fiber with an external diameter of 2.2 mm, strain relief 40 N
Construction type	OVK OptoQuick
Colour	grey
Type	OVKS 2,2
Order No.	936 200-002
Scope of delivery and accessories	
Scope of delivery	20 fiber optic plugs, each consisting of a plug body and a strain relief 1 polishing tool 1 operating instructions

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.