




## Product information PSW 5-20

Fiber Interfaces:Accessories Fiber Interfaces:Plug-in Power Supplies:PSW 5-20

<https://www.e-catalog.beldensolutions.com:443/link/57078-57141-57139-24575-38463/en/conf/ulistate>

Name	PSW 5-20
	
	plug-in power supply
<b>Delivery informations</b>	
Availability	available
<b>Product description</b>	
Description	plug-in power supply
Type	PSW 5-20
Order No.	943 008-001
<b>Electrical interfaces</b>	
Input voltage	90 to 260 VAC; 50 to 60 Hz
Current consumption	60 mA
Power consumption	-
Output voltage	+5 V
Output current	max. 2.0 A
Ripple voltage	max. 100 mVpp
<b>More Interfaces</b>	
Voltage output	extra-low voltage plug, design M8 acc. IEC 947-5-2
<b>Ambient conditions</b>	
Operating temperature	0 °C to +40 °C
Storage/transport temperature	-40 °C to +70 °C
Relative humidity (non-condensing)	10% to 95%
<b>Mechanical construction</b>	
Weight	200 g
<b>EMC interference immunity</b>	
EN 61000-6-2 Immunity for industrial environments	EN 61000-6-2
<b>EMC emitted immunity</b>	
EN 55022	EN 55022 limit class B, EN 55024
<b>Approvals</b>	
Safety of information technology equipment	IEC 60950, IEC 60065
<b>Scope of delivery and accessories</b>	
Scope of delivery	device

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.