


AX100077 Faceplates and Panels - FiberExpress Rack Mount Patch Panel 3U



For more Information
please call

1-800-Belden1

General Description:

FiberExpress Patch Panel, Rack Mount, 3U, Black.

Usage (Overall)

Suitable Applications: FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

Related Parts: FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits

Physical Characteristics (Connectivity)

Capacity

Max. Capacity: 4 Strips; 48 Fibers (SC, SCD, ST, FC); 96 Fibers (LCD, MT-RJ). Two 8-inch Splice Tray Kit (A0649869), Two 12-inch Splice tray Kit (A0318904)

Access

Front Connection: Flush

Termination Area: Front Sliding Drawer

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.900	19.000	12.400

Materials

Materials:

Description	Material
Panel	Steel
Cover	Lexan

Color

Color: Black

Weight

Weight: 16 lbs.

Included Parts

Included Parts: 4 Screws (10x32); 5 Tie Wraps; Identification Label; Caution Label

Packaging

Packaging: Individually packaged in a cardboard box.

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Suitability

Suitability - Indoor: Yes

Notes (Overall)

Notes: For proper installation refer to Installation Guide P0746744 included with the product or visit our web site at <http://www.belden.com>

Product Family

Part Numbers:

Description	Item Number
FiberExpress Rack Mount PP 1U Black	AX100041
FiberExpress Rack Mount PP 2U Black	AX100068
FiberExpress Rack Mount PP 3U Black	AX104934
FiberExpress Rack Mount PP 4U Black	AX100116

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

AX100077 Faceplates and Panels - FiberExpress Rack Mount Patch Panel 3U

Revision Number: 0 Revision Date: 05-31-2009

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.