



AX101085 Faceplates and Panels - FiberExpress Manager Shelf 19 in



For more Information
please call

1-800-Belden1



General Description:

FiberExpress Manager Shelf 19 in, Empty

Usage (Overall)

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room
Related Parts:	FiberExpress Manager Connector Module, Splice Holder Kit, Flex Kit

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	12 FiberExpress Manager Connector Modules
-----------------------	---

Access

Front Connection:	1 inch Pullout
--------------------------	----------------

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
7.000	19.000	16.000

Materials

Materials:

Description	Material
Panel	Steel
Door	Lexan

Color

Color:	Black
---------------	-------

Weight

Weight:	18 lbs.
----------------	---------

Included Parts

Included Parts:	screws, caution and ID labels, velcro strap, saddle, installation guide, cable ties, bend controllers
------------------------	---

Packaging

Packaging:	Individually packaged in a cardboard box.
-------------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/10/2008
MIL Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX101426 included with the product or visit our web site at <http://www.belden.com>

Product Family

Put Ups and Colors:

AX101085 Faceplates and Panels - FiberExpress Manager Shelf 19 in

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101085+CN	1 EA	49.655 LB			FIBEREXPRESS MANAGER, SH

Revision Number: 0 Revision Date: 06-04-2009

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.