


## RS-485 Cable Offering



Shield	Product Code	PR	AWG	Jacket	Rating	Application
SF/UTP	3074F	1	18AWG	Indust PVC	CMG/ITC/PLTC/600V TC	Industrial & other harsh environment
SF/UTP	3105A	1	22AWG	Indust PVC	CM/PLTC	Industrial & other harsh environment
SF/UTP	3106A	1.5	22AWG	Indust PVC	CM/PLTC	Industrial & other harsh environment
SF/UTP	3107A	2	22AWG	Indust PVC	CM/PLTC	Industrial & other harsh environment
SF/UTP	3108A	3	22AWG	Indust PVC	CM/PLTC	Industrial & other harsh environment
SF/UTP	3109A	4	22AWG	Indust PVC	CM/PLTC	Industrial & other harsh environment
SF/UTP	3105DB	1	22AWG	CPE	CM/PLTC, UL Direct Burial	Industrial & other harsh environment
SF/UTP	3106DB	1.5	22AWG	CPE	CM/PLTC, UL Direct Burial	Industrial & other harsh environment
SF/UTP	3107DB	2	22AWG	CPE	CM/PLTC, UL Direct Burial	Industrial & other harsh environment
SF/UTP	3108DB	3	22AWG	CPE	CM/PLTC, UL Direct Burial	Industrial & other harsh environment
SF/UTP	3109DB	4	22AWG	CPE	CM/PLTC, UL Direct Burial	Industrial & other harsh environment
SF/UTP	3105T	1	22AWG	TP LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3106T	1.5	22AWG	TP LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3107T	2	22AWG	TP LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3108T	3	22AWG	TP LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3109T	4	22AWG	TP LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3105Z	1	22AWG	TS LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3106Z	1.5	22AWG	TS LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3107Z	2	22AWG	TS LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3108Z	3	22AWG	TS LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	3109Z	4	22AWG	TS LSNH	CMG/PLTC	Marine transportation & other harsh environment
SF/UTP	123105A	1	22AWG	Indust PVC	AIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	123106A	1.5	22AWG	Indust PVC	AIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	123107A	2	22AWG	Indust PVC	AIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	123108A	3	22AWG	Indust PVC	AIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	123109A	4	22AWG	Indust PVC	AIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	133105A	1	22AWG	Indust PVC	SIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	133106A	1.5	22AWG	Indust PVC	SIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	133107A	2	22AWG	Indust PVC	SIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	133108A	3	22AWG	Indust PVC	SIA, CM/PLTC	Industrial & other harsh environment
SF/UTP	133109A	4	22AWG	Indust PVC	SIA, CM/PLTC	Industrial & other harsh environment
S/FTP	9841	1	24AWG	PVC	CMG	Light industrial environment
S/FTP	9842	2	24AWG	PVC	CMG	Light industrial environment
S/FTP	9843	3	24AWG	PVC	CMG	Light industrial environment
S/FTP	9844	4	24AWG	PVC	CMG	Light industrial environment
S/FTP	9841ZH	1	24AWG	LSNH	CMG	Light industrial environment
S/FTP	9842ZH	2	24AWG	LSNH	CMG	Light industrial environment
S/FTP	9843ZH	3	24AWG	LSNH	CMG	Light industrial environment
S/FTP	9844ZH	4	24AWG	LSNH	CMG	Light industrial environment
S/FTP	82841	1	24AWG	PVC	CMP	Light industrial environment
S/FTP	82842	2	24AWG	PVC	CMP	Light industrial environment
S/FTP	82843	3	24AWG	PVC	CMP	Light industrial environment
S/FTP	82844	4	24AWG	PVC	CMP	Light industrial environment
S/FTP	89841	1	24AWG	FEP	CMP	Light industrial environment
S/FTP	89842	2	24AWG	FEP	CMP	Light industrial environment
SF/UTP	7200A	1	24AWG	Indust PVC	CM, High Flex 1M 10XOD	Robotic, industrial & other harsh environment
SF/UTP	7201A	2	24AWG	Indust PVC	CM, High Flex 1M 10XOD	Robotic, industrial & other harsh environment
SF/UTP	7202A	3	24AWG	Indust PVC	CM, High Flex 1M 10XOD	Robotic, industrial & other harsh environment
SF/UTP	7203A	4	24AWG	Indust PVC	CM, High Flex 1M 10XOD	Robotic, industrial & other harsh environment