


## AX100536 Faceplates and Panels - FiberExpress Adapter Strip, loaded 6 FC Adapters



For more Information  
please call

1-800-Belden1

### General Description:

FiberExpress Adapter Strip, loaded 6 FC Multimode/Singlemode Adapters Black

### Usage (Overall)

|                               |   |
|-------------------------------|---|
| <b>Suitable Applications:</b> | FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room |
| <b>Related Parts:</b>         | FiberExpress Rack Mount Patch Panel, FiberExpress Wall Mount Patch Panel          |

### Physical Characteristics (Connectivity)

#### Capacity

|                       |   |
|-----------------------|---|
| <b>Max. Capacity:</b> | 6 Fibers, 6 FC Multimode/Singlemode Adapter |
|-----------------------|---|

#### Access

|                          |       |
|--------------------------|-------|
| <b>Front Connection:</b> | Flush |
| <b>Termination Area:</b> | Front |

#### Dimensions

##### Dimensions:

| Height (in.) | Width (in.) | Depth (in.) |
|--------------|-------------|-------------|
| 1.000        | 6.500       | 0.580       |

#### Materials

##### Materials:

| Description    | Type | Material         |
|----------------|------|------------------|
| Strip          |      | Steel            |
| Connector Body | FC   | Metal            |
| Adapter Sleeve |      | Zirconia-Ceramic |

#### Color

|               |       |
|---------------|-------|
| <b>Color:</b> | Black |
|---------------|-------|

#### Weight

|                |            |
|----------------|------------|
| <b>Weight:</b> | 0.205 lbs. |
|----------------|------------|

#### Included Parts

|                        |           |
|------------------------|-----------|
| <b>Included Parts:</b> | Dust Caps |
|------------------------|-----------|

#### Packaging

|                   |  |
|-------------------|--|
| <b>Packaging:</b> | Individually packaged in a plastic bag. Standard pack of 30 units. |
|-------------------|--|

### Mechanical Characteristics (Connectivity)

#### Termination Interface:

| Termination | Connection       | Durabilities |
|-------------|------------------|--------------|
| Front       | Mated Connection | 500 cycles   |
| Rear        | Mated Connection | 500 cycles   |

|                                   |             |
|-----------------------------------|-------------|
| <b>Cable/Connector Retention:</b> | 11.250 lbs. |
|-----------------------------------|-------------|

|                                   |                |
|-----------------------------------|----------------|
| <b>Storage Temperature Range:</b> | -40°C To +75°C |
|-----------------------------------|----------------|

|                                     |                |
|-------------------------------------|----------------|
| <b>Operating Temperature Range:</b> | -10°C To +60°C |
|-------------------------------------|----------------|

### Applicable Specifications and Agency Compliance (Overall)

#### Suitability

|                              |     |
|------------------------------|-----|
| <b>Suitability - Indoor:</b> | Yes |
|------------------------------|-----|

### Transmission Characteristics (Connectivity)

### Notes (Overall)

**Notes:** For additional information about this product, visit our web site at <http://www.belden.com>.

#### Product Family

##### Part Numbers:

| Description   | Multimode | Singlemode | Others |
|---|-----------|------------|--------|
| FiberExpress Strip Single density loaded with 6 ST Compatible Adapters  | AX100088  | AX100534   | -      |
| FiberExpress Strip Double density loaded with 12 ST Compatible Adapters | AX100080  | AX100528   | -      |
| FiberExpress Strip Single density loaded with 3 SC Duplex Adapters      | AX100094  | AX101407   | -      |
| FiberExpress Strip Single density loaded with 6 SC Simplex Adapters     | AX100092  | AX100538   | -      |

## AX100536 Faceplates and Panels - FiberExpress Adapter Strip, loaded 6 FC Adapters

|   |          |          |          |
|---|----------|----------|----------|
| FiberExpress Strip Double density loaded with 6 SC Duplex Adapters                      | AX100098 | AX101409 | -        |
| FiberExpress Strip Double density loaded with 12 SC Simplex Adapters                    | AX100084 | AX100532 | -        |
| FiberExpress Strip Single density loaded with 6 FC Adapters Multimode/Singlemode        | -        | -        | AX100536 |
| FiberExpress Strip Double density loaded with 12 FC Adapters Multimode/Singlemode       | -        | -        | AX100530 |
| FiberExpress Strip Single density loaded with 6 LC Duplex Adapters                      | AX101729 | AX101731 | -        |
| FiberExpress Strip Double density loaded with 12 LC Duplex Adapters                     | AX101741 | AX101743 | -        |
| FiberExpress Strip MT-RJ Single density loaded with 6 MT-RJ Black Multimode/Singlemode  | -        | -        | AX101115 |
| FiberExpress Strip MT-RJ Double density loaded with 12 MT-RJ Black Multimode/Singlemode | -        | -        | AX101117 |
| FiberExpress Strips Blank   | -        | -        | AX100066 |

### Put Ups and Colors:

| Item #      | Putup | Ship Weight | Color | Notes | Item Desc                |
|-------------|-------|-------------|-------|-------|--------------------------|
| AX100536+TW | 1 EA  | 0.084 KG    |       |       | ADAP. STRIP 6-FC, MM-SM, |

Revision Number: 0 Revision Date: 06-19-2009

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.