

AX103116 Faceplates and Panels - KeyConnect Patch Panel - KeyConnect



For more Information
please call

1-800-Belden1



General Description:

KeyConnect Patch Panel, 72-port, 2U, Black (Empty)

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 2400 and 1200.
Related Parts:	- Compatible with 10GX, CAT6+ and CAT5E KeyConnect Modular Jacks as well as KeyConnect Multimedia Modules.

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	72 connectors
-----------------------	---------------

Access

Front Connection:	Flush
Termination Area:	Rear

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
3.500	19.000	1.300

Materials

Materials:

Description	Material
Panel	Steel

Color

Color:	Black
---------------	-------

Weight

Weight:	1.800 lbs.
----------------	------------

Included Parts

Included Parts:	8 Screws (10x32); 8 Screws (12x24); 4 Label Holders; 1 Printable LabelFlex Half-Sheet; 4 Velcro Straps; 4 Rear Cable Management Brackets; 2 Management Bars; 1 Installation Guide
------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Packaging

Packaging:	Individually packaged in a cardboard box.
-------------------	-------------------------------------------

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/10/2008
MIL Order #39 (China RoHS):	Yes
Safety Listing:	ACA, Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX104691 included with the product or visit our web site at <http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf>

AX103116 Faceplates and Panels - KeyConnect Patch Panel - KeyConnect

Product Family

Part Numbers:

Description	Item Number
KeyConnect PP 1U24P, Black	AX103114
KeyConnect PP 1U48P, Black	AX103121
KeyConnect PP 2U48P, Black	AX103115
KeyConnect PP 2U72P, Black	AX103116
KeyConnect PP 3U96P, Black	AX105371

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX103116	1 EA	2.978 LB			KCONN PATCH PANEL 72-P 2U BLK

Revision Number: 0 Revision Date: 12-12-2013

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.