

AX105300 Faceplates and Panels - Angled Patch Panel - KeyConnect



For more Information
please call

1-800-Belden1



General Description:

Angled Patch Panel, 24-port, 1U with 10GX RJ45 Coupler, Black

Image

Image:



Usage (Overall)

Suitable Applications:	- IBDN System 10GX, TIA Category 6A, 10GBASE-T
Related Parts:	- Compatible with 10GX Patch Cord and 10GX Pre-Terminated Cable Assemblies.

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	24 connectors
----------------	---------------

Access

Front Connection:	Angled
Termination Area:	Rear

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
1.750	19.000	10.440

Materials

Materials:

Description	Material
Panel	Steel

Color

Color:	Black
--------	-------

Weight

Weight:	2.700 lbs.
---------	------------

Included Parts

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 2 Label Holder; 2 Velcro Straps; 2 Rear Cable Management Bracket; 1 Bar.
-----------------	--

Packaging

Packaging:	Individually packaged in a cardboard box.
------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
----------------------------	----------------

AX105300 Faceplates and Panels - Angled Patch Panel - KeyConnect

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/10/2008

MIL Order #39 (China RoHS): Yes

Safety Listing: Bi-national Standard Listed

Suitability

Suitability - Indoor: Yes

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For more information visit our web site at <http://www.belden.com>

Notes (Cont'd.): Refer to AX102283 for the Specifications of the Modular Jacks.

Product Family

Part Numbers:

Description	Item Number
Angled PP 1U24P (empty), Black	AX104599
Angled PP 2U48P (empty), Black	AX104601
Angled PP 2U48P Vertical Labeling (empty), Black	AX104601-VLB
Angled PP 1U24P 10GX Coupler, Black	AX105300
Angled PP 2U48P 10GX Coupler, Black	AX105301
Angled PP 1U24P CAT6+ Coupler, Black	AX105349
Angled PP 2U48P CAT6+ Coupler, Black	AX105350
Angled PP 1U24P CAT5E Modular Jack, Black	AX105357
Angled PP 2U48P CAT5E Modular Jack, Black	AX105358
Angled PP 1U24P CAT6+ Modular Jack, Black	AX105360
Angled PP 2U48P CAT6+ Modular Jack, Black	AX105361
Angled PP 1U24P 10GX Modular Jack, Black	AX105363
Angled PP 2U48P 10GX Modular Jack, Black	AX105364

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX105300	1 EA	3.339 LB			10GX KCONN ANG.COUPLER PP 24

Revision Number: 0 Revision Date: 09-06-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.