

## AX101764 Modular Connectors - MediaFlex Filler Insert 2-unit



For more Information  
please call

1-800-Belden1



### General Description:

Kit of 10 Mdediflex Filler Inserts, 2U, flush, black

### Usage (Overall)

**Related Parts:** Compatible with MediaFlex Faceplate

### Physical Characteristics (Connectivity)

#### Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
0.925	2.050	0.410

#### Materials

Materials:

Description	Material
Insert	Plastic - UL940V-0

#### Color

**Color:** Black

#### Weight

**Weight:** 0.100 lbs.

#### Packaging

**Packaging:** 10 inserts packaged in a suitable plastic bag.

### Mechanical Characteristics (Connectivity)

<b>Storage Temperature Range:</b>	-40°C To +70°C
<b>Installation Temperature Range:</b>	-10°C To +60°C
<b>Operating Temperature Range:</b>	-10°C To +60°C
<b>Tool Compatibility:</b>	Release Tool (AX101185)

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

<b>EU Directive 2002/95/EC (RoHS):</b>	Yes
<b>EU RoHS Compliance Date (mm/dd/yyyy):</b>	07/01/2006
<b>MII Order #39 (China RoHS):</b>	Yes
<b>Safety Listing:</b>	ACA, Bi-national Standard Listed

#### Suitability

**Suitability - Indoor:** Yes - Indoor

### Transmission Characteristics (Connectivity)

### Notes (Overall)

**Notes:** Visit our web site at <http://www.belden.com>

### Product Family

Part Number List:

Description	Gray	Almond	Elec White	Black
MediaFlex Filler Insert 1-unit	AX101757	AX101758	AX101759	AX101760
MediaFlex Filler Insert 2-unit	AX101761	AX101762	AX101763	AX101764

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101764	1 EA	0.100 LB			KIT MFLX FILLER INSERT(10/PK)

## AX101764 Modular Connectors - MediaFlex Filler Insert 2-unit

Revision Number: 0    Revision Date: 08-08-2012

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.