

AX102431 Faceplates and Panels - MediaFlex Faceplate Kit KeyConnect 6-Port, Flush, Single-Gang



For more Information
please call

1-800-Belden1



General Description:

MediaFlex Faceplate Kit for KeyConnect Modules 6-Port, Flush, Single-Gang

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200.
Related Parts:	- Compatible with REVConnect Jacks (UTP & STP), KeyConnect Jacks (UTP) and Keyconnect Multimedia Modules. See notes if using KeyConnect Shielded (STP) Jacks.

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	6 ports
-----------------------	---------

Access

Front Connection:	Flush
--------------------------	-------

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
4.500	3.020	0.455

Materials

Materials:

Description	Material
Faceplate	Plastic - UL94V-0
Insert	Plastic - UL94V-0

Color

Color:	Elec. White
---------------	-------------

Weight

Weight:	0.100 lbs.
----------------	------------

Included Parts

Included Parts:	Windows, paper, 6-32 screws, 2-port insert, 2U blank insert, blank, installation guide
------------------------	--

Packaging

Packaging:	Individually packaged in a suitable plastic bag
-------------------	---

Mechanical Characteristics (Connectivity)

Footprint/Type:	KeyConnect
Connector/Hardware Retention:	20 lbs.
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA, c(UL)us Listed

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

AX102431 Faceplates and Panels - MediaFlex Faceplate Kit KeyConnect 6-Port, Flush, Single-Gang

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: Please contact Tech Support if using Shielded KeyConnect jacks (AX104562, AX104595, AX104596) for compatibility verification.

Product Family

Part Numbers:

Description	Gray	Almond	Elec White	Black	Ivory
MediaFlex Faceplate Kit KeyConnect Single-Gang 2-Port Flush	AX104493	AX104494	AX104495	AX104496	AX105777
MediaFlex Faceplate Kit KeyConnect Single-Gang 4-Port Flush	AX104485	AX102428	AX102429	AX104489	AX105778
MediaFlex Faceplate Kit KeyConnect Single-Gang 6-Port Flush	AX104486	AX102430	AX102431	AX104490	AX105779
MediaFlex Faceplate Kit KeyConnect Single-Gang 2-Port Angled	AX104497	AX104498	AX104499	AX104500	AX105780
MediaFlex Faceplate Kit KeyConnect Single-Gang 4-Port Angled	AX104487	AX102432	AX102433	AX104491	AX105781
MediaFlex Faceplate Kit KeyConnect Double-Gang 6-Port Flush	AX105769	AX102523	AX102524	AX105770	AX105782
MediaFlex Faceplate Kit KeyConnect Double-Gang 8-Port Flush	AX105771	AX102520	AX102520	AX105772	AX105783
MediaFlex Faceplate Kit KeyConnect Double-Gang 12-Port Flush	AX104488	AX102434	AX102435	AX104492	AX105784
MediaFlex Faceplate Kit KeyConnect Double-Gang 6-Port Angled	AX105773	AX102521	AX102522	AX105774	AX105785
MediaFlex Faceplate Kit KeyConnect Double-Gang 8-Port Angled	AX105775	AX102436	AX102437	AX105776	AX105786

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102431	1 EA	0.102 LB			KCONN MFLEX FP KIT 6-P ELEC WH

Revision Number: 0 Revision Date: 08-16-2017

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.