


PVC

UL AWM Style 1061 300V, 80°C (CSA AWM)

Product Description

Tinned copper, semi-rigid PVC insulation (solid conductors suitable for wire wrap applications).

Solid Conductor



Stranded Conductor



Part No.	AWG (stranding)	Insulation Thickness		Nominal OD		Standard Lengths		Standard Unit Weight		Stock Colors (See Color Codes Chart on Page 3.29)
		Inch	mm	Inch	mm	Ft.	m	Lbs.	kg	
300V, 80°C (UL & CSA)										
UL AWM Style 1061 • CSA AWM										
9978	30 (solid)	.010	.25	.030	.76	100	30.5	.1	.05	1-5, 7-10, 13
						1000	304.8	1.0	.50	1-5, 7-10, 13
9987	30 (7x38)	.010	.25	.032	.81	100	30.5	.1	.05	2, 7-10
						1000	304.8	1.0	.50	2, 7-10
9977	28 (solid)	.010	.25	.033	.84	100	30.5	.1	.05	1-5, 7-10, 13
						1000	304.8	1.0	.50	1-5, 7-10, 13
9986	28 (7x36)	.010	.25	.035	.89	100	30.5	.1	.05	1-5, 7-10, 13
						1000*	304.8	2.0	1.00	1-5, 7-10, 13
						10000*	3048.0	10.0	4.50	2, 4, 10, 13
9976	26 (solid)	.010	.25	.036	.91	100	30.5	.2	.10	1-5, 7-10, 13
						1000*	304.8	2.0	.90	1-5, 7-10, 13
9985	26 (7x34)	.010	.25	.039	.99	100	30.5	.2	.10	1-5, 7-10, 13
						1000*	304.8	2.0	.90	1-5, 7-10, 13
						5000*	1524.0	10.0	4.50	4, 5, 10, 13
9975	24 (solid)	.010	.25	.040	1.02	100	30.5	.2	.10	1-5, 7-10, 13
						1000*	304.8	3.0	1.40	1-5, 7-10, 13
						5000*	1524.0	10.0	4.50	2, 10
9984	24 (7x32)	.010	.25	.044	1.12	100	30.5	.2	.10	1-5, 7-10, 13
						1000*	304.8	3.0	1.40	1-5, 7-10, 13
						5000*	1524.0	10.0	4.50	2, 3, 5, 10, 13
9979	22 (solid)	.010	.25	.047	1.19	1000*	304.8	4.0	1.80	1-5, 7-10, 13
						5000*	1524.0	15.0	6.80	9
9983	22 (7x30)	.010	.25	.050	1.27	100	30.5	.3	.10	1-5, 7-10, 13
						1000*	304.8	4.0	1.80	1-5, 7-10, 13
						5000*	1524.0	15.0	6.80	1, 9, 13
						10000*	3048.0	30.0	13.60	1-3, 9, 10
9982	20 (7x28)	.010	.25	.057	1.45	100	30.5	.5	.20	1-5, 7-10, 13
						1000*	304.8	5.0	2.30	1-5, 7-10, 13
						5000*	1524.0	20.0	9.07	9, 13
9917	20 (10x30)	.010	.25	.056	1.42	1000*	304.8	5.0	2.30	1-4, 7, 9, 10
9911	18 (16x30)	.010	.25	.067	1.70	1000	304.8	7.0	3.20	1-5, 7-10, 13
9981	18 (19x30)	.010	.25	.066	1.68	100	30.5	.8	.40	1-5, 7-10, 13
						1000*	304.8	7.0	3.20	1-5, 7-10, 13
9980	16 (19x28)	.010	.25	.078	1.98	100	30.5	1.3	.60	1-5, 7-10, 13
						1000*	304.8	11.0	5.00	1-5, 7-10, 13
9909	16 (26x30)	.010	.25	.080	2.03	100*	30.5	1.2	.50	3, 7
						1000*	304.8	11.0	5.00	2-5, 7, 9, 10

*Stripe colors on stock solid colors. Striping adder of \$8.00/1000 ft. for one or two stripes. 10,000 ft. minimum order for color combination. Put-up will be subject to two pieces ±10% per spool with a minimum length of 100 ft.