

1694A Coax - Low Loss Serial Digital Coax



For more Information
please call

1-800-Belden1



General Description:

RG-6/U Type, 18 AWG solid .040" bare copper conductor, gas-injected foam HDPE insulation, Duofoil® + tinned copper braid shield (95% coverage), PVC jacket.

Usage (Overall)

Suitable Applications: SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080p

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BC - Bare Copper	.040

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FHDPE - Foam High Density Polyethylene	.180

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Duofoil®	Tape	Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.274 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +75°C

Bulk Cable Weight: 41 lbs/1000 ft.

Max. Recommended Pulling Tension: 69 lbs.

Min. Bend Radius/Minor Axis: 2.750 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

1694A Coax - Low Loss Serial Digital Coax

RG Type: 6/U

Flame Test

UL Flame Test: UL1666 Vertical Shaft

CSA Flame Test: FT4

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black only.

Suitability - Aerial: Yes - Black only, when supported by messenger wire.

Suitability - Burial: No

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 1695A

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/ft)

0.106

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.2

Nominal Velocity of Propagation:

VP (%)

82

Nominal Delay:

Delay (ns/ft)

1.24

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.4

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.8

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1.000	0.240
3.580	0.440
5.000	0.520
6.000	0.570
7.000	0.610
10.000	0.710
12.000	0.780
25.000	1.080
67.500	1.650
71.500	1.690
88.500	1.860
100.000	1.950
135.000	2.240
143.000	2.300
180.000	2.570
270.000	3.170
360.000	3.690
540.000	4.500
720.000	5.300
750.000	5.400
1000.000	6.300
1500.000	7.800
2000.000	9.200
2250.000	9.800
3000.000	11.500

1694A Coax - Low Loss Serial Digital Coax

4500.000	14.500
6000.000	17.700

Max. Operating Voltage - UL:

Voltage
300 V RMS

Other Electrical Characteristic 1:

TDR Impedance: 75 +/- 1.5 Ohms

Other Electrical Characteristic 2:

Return Loss: Fixed bridge and termination.

Minimum Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
5.000	1600.000	23.000
1600.000	4500.000	21.000
4500.000	6000.000	15.000

Sweep Test

Sweep Testing:

100% Sweep tested 5 MHz to 6 GHz.

Misc. Information (Overall)

Notes (Overall)

Notes: Print legend includes sequential footage marks. Also available in 4.5 GHz multi-coax bundled versions. See 7710A through 7713A.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1694A N3UN1000	1,000 FT	45.000 LB	GREEN, MIL		#18 PE/GIFHDPE SH FR PVC
1694A N3U1000	1,000 FT	45.000 LB	GREEN, MIL	C	#18 PE/GIFHDPE SH FR PVC
1694A N3U5000	5,000 FT	225.000 LB	GREEN, MIL	C N	#18 PE/GIFHDPE SH FR PVC
1694A 0011000	1,000 FT	45.000 LB	BROWN	C	#18 PE/GIFHDPE SH FR PVC
1694A 0015000	5,000 FT	225.000 LB	BROWN	C N	#18 PE/GIFHDPE SH FR PVC
1694A 0021000	1,000 FT	45.000 LB	RED	C	#18 PE/GIFHDPE SH FR PVC
1694A 0025000	5,000 FT	225.000 LB	RED	C N	#18 PE/GIFHDPE SH FR PVC
1694A 0031000	1,000 FT	45.000 LB	ORANGE	C	#18 PE/GIFHDPE SH FR PVC
1694A 004N1000	1,000 FT	45.000 LB	YELLOW		#18 PE/GIFHDPE SH FR PVC
1694A 0041000	1,000 FT	45.000 LB	YELLOW	C	#18 PE/GIFHDPE SH FR PVC
1694A 0061000	1,000 FT	45.000 LB	BLUE, LIGHT	C	#18 PE/GIFHDPE SH FR PVC
1694A 0065000	5,000 FT	225.000 LB	BLUE, LIGHT	C N	#18 PE/GIFHDPE SH FR PVC
1694A 007N1000	1,000 FT	44.000 LB	VIOLET		#18 PE/GIFHDPE SH FR PVC
1694A 0071000	1,000 FT	45.000 LB	VIOLET	C	#18 PE/GIFHDPE SH FR PVC
1694A 0075000	5,000 FT	225.000 LB	VIOLET	C N	#18 PE/GIFHDPE SH FR PVC
1694A 0081000	1,000 FT	45.000 LB	GRAY	C	#18 PE/GIFHDPE SH FR PVC
1694A 0085000	5,000 FT	225.000 LB	GRAY	C N	#18 PE/GIFHDPE SH FR PVC
1694A 009N1000	1,000 FT	45.000 LB	WHITE		#18 PE/GIFHDPE SH FR PVC
1694A 0091000	1,000 FT	45.000 LB	WHITE	C	#18 PE/GIFHDPE SH FR PVC
1694A 010N1000	1,000 FT	45.000 LB	BLACK		#18 PE/GIFHDPE SH FR PVC
1694A 0101000	1,000 FT	45.000 LB	BLACK	C	#18 PE/GIFHDPE SH FR PVC
1694A 010500	500 FT	22.500 LB	BLACK	C	#18 PE/GIFHDPE SH FR PVC
1694A 0105000	5,000 FT	225.000 LB	BLACK	C N	#18 PE/GIFHDPE SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Revision Number: 18 Revision Date: 04-12-2017

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).