


1700S6 Multi-Conductor - Banana Peel® Jacketless Cables

DataTwist 350



For more Information
please call

1-800-Belden1



Description:

24 AWG bonded-pairs, solid bare copper conductors, non-plenum, Polyolefin insulation, rip cord, riser, see color code chart (below), PVC inner jacket (light blue or gray), no overall jacket.

Usage (Overall)

Suitable Applications:

Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 350MHz Enhanced Category 5e

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
24	24	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (in.)
PVC - Polyvinyl Chloride	.204

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
Unjacketed

Overall Cable

Overall Cabling Fillers:

Spline

Overall Cabling Color Code Chart:

Number	Color
1	1/ONE
2	2/TWO
3	3/THREE
4	4/FOUR
5	5/FIVE
6	6/SIX

Overall Nominal Diameter:

0.600 in.

Pair

Pair Color Code Chart:

Number	Color
--------	-------

1700S6 Multi-Conductor - Banana Peel® Jacketless Cables

1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
Bulk Cable Weight:	139 lbs/1000 ft.
Max. Recommended Pulling Tension:	1440 lbs.
Min. Bend Radius (Install)/Minor Axis:	0.600 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
Other Standards:	Individual leg: 11801 Category 5
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Individual leg: ANSI/TIA/EIA-568-B.2 Category 5e
Other Specification:	Individual leg: NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1701S6

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)	15
---------------------	----

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)	70
--------	----

Maximum Delay:

Delay (ns/100 m)	510
------------------	-----

Max. Delay Skew:

Delay Skew (ns/100 m)	25
-----------------------	----

Maximum Conductor DC Resistance:

1700S6 Multi-Conductor - Banana Peel® Jacketless Cables

DCR @ 20°C (Ohm/100 m)

9

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	63.3	63.3	20.0
4	4.0	56.3	56.3	52.3	52.3	23.0
8	5.7	51.8	51.8	46.1	46.1	24.5
10	6.4	50.3	50.3	43.9	43.9	25.0
16	8.1	47.3	47.3	39.1	39.1	25.0
20	9.2	45.8	45.8	35.2	35.2	25.0
25	10.3	44.3	44.3	34.1	34.1	24.3
31.25	11.6	42.9	42.9	31.3	31.3	23.6
62.5	16.8	38.4	38.4	21.6	21.6	21.5
100	21.7	35.3	35.3	17.1	17.1	20.1
155	27.7	32.5	32.5	4.7	4.7	19.0
200	32.0	30.8	30.8	3.0	3.0	19.0
250	36.4	29.3	29.3	>0	>0	18.0
300	40.5	28.2	28.2			18.0
310	41.3	27.9	27.9			18.0
350	44.3	27.2	27.2			17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.8
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.9
100	100 ± 15	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: Belden IBDN. Bundled version of 1700R. Jacket sequentially marked at 2 ft. intervals. US Patent #'s 5, 606, 151; 5, 734, 126; Banana Peel® US PATENT 7, 049, 523. Individual legs third party verified to TIA/EIA-568-B.2, Category 5e.

Put up and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1700S6 F2V1000	1,000 FT	161.000 LB	GRAY, DEC	C	CAT5E+ BANANA PEEL 6X CMR REEL
1700S6 F2V500	500 FT	83.500 LB	GRAY, DEC	C	CAT5E+ BANANA PEEL 6X CMR REEL
1700S6 0061000	1,000 FT	161.000 LB	BLUE, LIGHT	C	CAT5E+ BANANA PEEL 6X CMR REEL
1700S6 006500	500 FT	83.500 LB	BLUE, LIGHT	C	CAT5E+ BANANA PEEL 6X CMR REEL

1700S6 Multi-Conductor - Banana Peel® Jacketless Cables

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 05-06-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.