


7813LC Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

For more Information
please call

1-800-Belden1



Description:

23 AWG Bonded-Pairs, Solid Bare Copper Conductors, Plenum & Limited Combustible, FEP Teflon® Insulation, Twisted Pairs, Central Filler, FEP Teflon Jacket

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155 ATM, 622 ATM, 250MHz Category 6, Enviroments benefitting from Limited Combustible Cable

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	23	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Teflon	FEP - Fluorinated Ethylene Propylene

Outer Jacket Diameter:

Nom. Dia. (in.)
0.214

Overall Cable

Overall Cabling Separator Material: Central Filler

Overall Nominal Diameter: 0.214 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +150°C

Bulk Cable Weight: 28 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

7813LC Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

Min. Bend Radius (Install)/Minor Axis: 1 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, FHC 25/50

NEC Articles: 800

CEC/C(UL) Specification: CMP

Other Standards: ISO/IEC 11801 ed 2.1 (2008) Class E

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Telecommunications Standards: Category 6 - TIA 568.C.2

Other Specification: UL verified to Category 6

Applicable Patents:

Country	Patent
US	5606151
US	5734126

Flame Test

UL Flame Test: NFPA 262 Plenum Flame Test (UL910)(FT6), UL723 (NFPA 255)

C(UL) Flame Test: FT6

CSA Flame Test: FT6

Plenum/Non-Plenum

Plenum (Y/N): Yes

Non-Plenum Number: 2412

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)
72

Maximum Delay:

Delay (ns/100 m)
537 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
8.2

7813LC Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
5

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	74.3	72.3	72.3	70.3	20.0	na
4	3.8	65.3	63.3	61.5	59.5	23.0	na
8	5.3	60.8	58.8	55.4	53.4	24.5	na
10	6.0	59.3	57.3	53.3	51.3	25.0	na
16	7.6	56.2	54.3	48.7	46.7	25.0	na
20	8.5	54.8	52.8	46.3	44.3	25.0	na
25	9.5	53.3	51.3	43.8	41.8	24.3	na
31.25	10.7	51.9	49.9	41.2	39.2	23.6	na
62.5	15.4	47.4	45.4	32.0	30.0	21.5	na
100	19.8	44.3	42.3	24.5	22.5	20.1	na
155	25.2	41.5	39.5	16.3	14.3	18.8	na
200	29.0	39.8	37.8	10.8	8.8	18.0	na
250	32.8	38.3	36.3	5.5	3.5	17.3	na

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	67.8	64.8
4	100 ± 15	100 ± 15	55.8	52.8
8	100 ± 15	100 ± 15	49.7	46.7
10	100 ± 15	100 ± 15	47.8	44.8
16	100 ± 15	100 ± 15	43.7	40.7
20	100 ± 15	100 ± 15	41.8	38.8
25	100 ± 15	100 ± 15	39.8	36.8
31.25	100 ± 15	100 ± 15	37.9	34.9
62.5	100 ± 15	100 ± 15	31.9	28.9
100	100 ± 15	100 ± 15	27.8	24.8
155	100 ± 22	100 ± 15	23.9	20.9
200	100 ± 22	100 ± 15	21.8	18.8
250	100 ± 32	100 ± 15	19.8	16.8

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to ANSI/TIA-568-C.2, Category 6.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7813LC 006U1000	1,000 FT	34.000 LB	BLUE, LIGHT		CAT6 4PRB U/UTP LC BOX
7813LC 006I1000	1,000 FT	37.000 LB	BLUE, LIGHT	C	CAT6 4PRB U/UTP LC REEL
7813LC 009U1000	1,000 FT	34.000 LB	WHITE		CAT6 4PRB U/UTP LC BOX
7813LC 009I1000	1,000 FT	37.000 LB	WHITE	C	CAT6 4PRB U/UTP LC REEL

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 05-03-2011

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not

7813LC Multi-Conductor - Enhanced Category 6 Bonded-Pair Cable

ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.