




REPRESENTATIVE IMAGE

Product: [5000UP](#) 

Audio Cable, 2 Conductor 12 AWG, BC, Unshielded, CL3

Product Description

Commercial Audio Cable, Rated-CL3, 2-12 AWG highly flexible stranded bare copper conductors with PVC insulation, PVC jacket with ripcord

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls |
|------------------------|---|

Construction Details

Conductor

| Element | Number of Element | AWG | Stranding | Material |
|--------------|-------------------|-----|-----------|------------------|
| Conductor(s) | 2 | 12 | 65x30 | BC - Bare Copper |

Insulation

| Element | Material | Thickness [in.] | Color Code |
|--------------|--------------------------|-----------------|--------------|
| Conductor(s) | PVC - Polyvinyl Chloride | 0.023 | Black, White |

Outer Jacket Material

| Material | Thickness | Nom. Diameter | Ripcord |
|--------------------------|-----------|---------------|---------|
| PVC - Polyvinyl Chloride | 0.018 in | 0.312 in | Yes |

| | |
|---------------------------|----------|
| Cable Diameter (Nominal): | 0.312 in |
|---------------------------|----------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Max. Current |
|--------------|--------------------|-------------------------------|------------------------------|
| Conductor(s) | 1.56 Ohm/1000ft | 32 pF/ft | 26 Amps per conductor @ 25°C |

Voltage

| UL Voltage Rating |
|-------------------|
| 300 V (CL3) |

Mechanical Characteristics

Temperature

| UL Rating | Operating |
|-----------|----------------|
| 75°C | -20°C to +75°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 3 in | 3.1 in |

| | |
|--------------------|---------------|
| Max. Pull Tension: | 169 lbs |
| Bulk Cable Weight: | 59 lbs/1000ft |

Standards and Compliance

| | |
|---------------------------------|---|
| Environmental Suitability: | Indoor (Not Riser or Plenum), Indoor |
| Flammability / Fire Resistance: | UL1685 (FT4 Loading), FT4, 1202, IEC 60332-1-2 |
| NEC / UL Compliance: | Article 725, CL3 |
| CPR Euroclass: | Eca |
| European Directive Compliance: | EU CE Mark, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.298 Revision Date: 08-12-2020 |
|----------------------|--|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.