

XFI48U2848-S005 SERVER RACK 48RU/44OU x 28w x 48d

- 89.125h x 28w x 48d
- WELDED STEEL FRAME CONSTRUCTION w/ REINFORCED CORNER POSTS
- HEAVY DUTY CASTERS
- HEAVY DUTY LEVELING LEGS
- COLOR: CARDINAL WHITE (C031-WH120) SEMI GLOSSS TEXTURE

- (2) PAIR FULLY ADJUSTABLE AND REVERSIBLE EIA/OCF RAILS 48RU/44OU
- RAILS MOUNTED IN EIA CONFIGURATIONS
- SQUARE HOLE TYPE EIA SIDE FOR CAGE NUTS
- (50) M6 MOUNTING HARDWARE INCLUDED
- RAIL FINISH IS CLEAR ZINC PLATED
- NUMERICAL MARKINGS FOR EACH RACK UNIT w/ UNIT 1 STARTING @ BOTTOM

- FULL SIZE 78% PERFORATED CONTOUR FRONT & REAR DOOR
- LOCKING SWING HANDLE

CONTOUR PERFORATED DOORS ADD 2.60 INCHES (PER DOOR) TO FRAME DEPTH DIMENSION

- (3)PC TOP PANEL
- FRONT & REAR PANELS HAVE 5-1/4" DIA KNOCKOUTS
- CENTER PANEL IS SOLID
- (4) GROMMETS ON FRONT & REAR PANELS

- PARTIAL BOTTOM PANEL w/ REAR CABLE OPENING

- FLUSH MOUNTED SIDE PANELS w/ TAMPER RESISTANT SCREWS


- (2) 3.5" VERTICAL PDU PANELS MOUNTED IN REAR

- (2) 2.0" VERTICAL LACING PANELS MOUNTED IN REAR

- (2) 6.0" VERTICAL LACING PANELS MOUNTED IN REAR


- BOTTOM FRONT SKIRT

- BOLT TOGETHER KIT w/ STRAP



78% PERF CONTOUR FRONT DOOR w/ LOCKING SWING HANDLE
PERF PATTERN REMOVED FOR CLARITY

48RU SQ. HOLE EIA RAIL KIT w/ (2) KNOCKOUTS IN THE FRONT & REAR RAILS



89.125
48RU / 44OU

48.00
(FRAME ONLY)

28.00

BOTTOM PANEL w/ REAR CABLE OPENING

BELDEN			
THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED.			
XFI48U2848-S005 / SERVER RACK 48RU/44OU x 28w x 48d			
APPROVED BY:	RCG	DRAWING AUTHOR:	RCG
APPROVAL DATE:	11/15/17		
UNITS:	INCH	Sheet 1 of 1	D
SCALE:	1:8	DATE	11/15/2017
			SUBMITTAL

REV	DESCRIPTION	BY	DATE