



**Product:** [DCX-CABV-KIT01B](#)

DCX Cable Distribution Attachment Kit, Black

### Product Description

DCX Cable Distribution Attachment Kit (1 Bracket w/ (2) Plastic Holders, up to 24 LPM Transitions per Holder), Black

### Technical Specifications

#### Product Overview

Environmental Space:	Indoor
Suitable Applications:	Optical Distribution Frame, Data Centers, Central Equipment Room

#### Construction

Weight:	1.150 lbs
Height:	5.270 in
Width:	3.370 in
Length:	3.930 in

#### Physical Specifications

Max Capacity:	48 LPM Transitions
---------------	--------------------

#### Temperature Range

Operating Temp Range:	-10°C to +60°C
Storage Temp Range:	-10°C to +75°C

#### Product Material

##### Materials

Description	Material	Color
Cable Distribution Manager	PC/ABS	Black
Cable Distribution Bracket	Steel	Black

#### Standards

EU RoHS Compliance Date (yyyy-mm-dd):	2013-01-11
MII Order #39 (China RoHS):	EUP 50

#### Part Number

Included Parts:	Hardware kit: #10-32 screw for metal (2x), Quick Start Guide document
Related Parts:	DCX Frame Module & Patch Panel

##### Variants

Item #	Length
DCX-CABV-KIT01B	3.930 in

#### Product Notes

Packaging:	Each item is packaged in a cardboard box
Notes:	For more information, refer to Quick Start Guide PX106858 (English) or visit our web site at <a href="http://www.belden.com/dcx">http://www.belden.com/dcx</a>

## History

Update and Revision:	Revision Number: 0.15 Revision Date: 04-28-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.