




FiberExpress (FX) Hybrid Copper-Fiber Cables allow end-users to take advantage of DC power and fiber in one cable to safely deliver low-voltage power and data over long distances to remote locations where standard power is unavailable or too costly to install. Hybrid cable technology offers installation and labor savings by requiring just a single cable pull. Various cable constructions offer unlimited application flexibility.

Standards:

- ICEA S-120-742
- RoHS
- ANSI/TIA-568-C.3



	Temperature Range	
	Riser	Plenum
Operating	-20°C to +70°C -4°F to +158°F	0°C to +70°C 32°F to +158°F
Storage	-40°C to +70°C -40°F to +158°F	-40°C to +70°C -40°F to +158°F
Installation	-10°C to +60°C 14°F to +140°F	0°C to +60°C 32°F to +140°F

Glass Type	Fiber Grade Code (x)	Subunit and Jacket Color	Operating Wavelength (nm)	Max Attenuation (dB/km)	Min. OFL Bandwidth (MHz-km)	Min. Laser Bandwidth (MHz-km)	1 Gigabit Ethernet Min. Link Length (meters)	10 Gigabit Ethernet Min. Link Length (meters)
OM3 - 50/125mm Multi-Mode	3	Aqua	850/1300	3.0/1.0	1500/500	2000/-	1000/550	300/-
OM4 - 50/125mm Multi-Mode	4	Erika Violet	850/1300	3.0/1.0	3500/500	4700/-	1100/550	400/-
OS2 - Single Mode	S	Yellow	1310/1550	0.5/0.5	-	-	5000/-	10,000/40,000

OM2 Fiber available upon Request

LSZH - UL Type CL3R-OF – 3mm Sub Units

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
12	2	HIxB0020212LC	See Table	0.327 (8.3)	76 (113)	300 (1330)	90 (400)
14	2	HIxB0020214LC	See Table	0.327 (8.3)	76 (113)	300 (1330)	90 (400)

¹ Substitute (x) with Fiber Grade Code

LSZH - UL Type CMR-OF – 3mm Sub Units

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
16	2	HIxB0020216LC	See Table	0.300 (7.6)	48 (71)	300 (1330)	90 (400)
18	2	HIxB0020218LC	See Table	0.300 (7.6)	43 (64)	300 (1330)	90 (400)
20	2	HIxB0020220LC	See Table	0.318 (8.1)	38 (57)	300 (1330)	90 (400)

¹ Substitute (x) with Fiber Grade Code

LSZH - UL Type CL3R-OF – 3mm Sub Units – Aluminum Interlocked Armor

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
12	2	HIxB0020212CC	See Table	0.584 (14.8)	171 (254)	300 (1330)	90 (400)
14	2	HIxB0020214CC	See Table	0.584 (14.8)	171 (254)	300 (1330)	90 (400)

¹ Substitute (x) with Fiber Grade Code

LSZH - UL Type CMR-OF – 3mm Sub Units – Aluminum Interlocked Armor

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
16	2	HIxB0020216CC	See Table	0.554 (14.1)	137 (204)	300 (1330)	90 (400)
18	2	HIxB0020218CC	See Table	0.554 (14.1)	132 (196)	300 (1330)	90 (400)
20	2	HIxB0020220CC	See Table	0.574 (14.6)	131 (195)	300 (1330)	90 (400)

¹ Substitute (x) with Fiber Grade Code

LSZH - UL Type CL3R-OF – 2mm Sub Units

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
12	2	HIxB0020212LB	See Table	0.312 (7.9)	73 (109)	300 (1330)	90 (400)
14	2	HIxB0020214LB	See Table	0.275 (7.0)	52 (77)	300 (1330)	90 (400)
1 Substitute (x) with Fiber Grade Code							

LSZH - UL Type CMR-OF – 2mm Sub Units

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
16	2	HIxB0020216LB	See Table	0.260 (6.6)	41 (61)	300 (1330)	90 (400)
18	2	HIxB0020218LB	See Table	0.254 (6.5)	35 (52)	300 (1330)	90 (400)
20	2	HIxB0020220LB	See Table	0.227 (5.8)	31 (46)	300 (1330)	90 (400)
1 Substitute (x) with Fiber Grade Code							

LSZH - UL Type CL3R-OF – 2mm Sub Units – Aluminum Interlocked Armor

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
12	2	HIxB0020212CB	See Table	0.564 (14.3)	164 (244)	300 (1330)	90 (400)
14	2	HIxB0020214CB	See Table	0.534 (13.6)	137 (204)	300 (1330)	90 (400)
1 Substitute (x) with Fiber Grade Code							

LSZH - UL Type CMR-OF – 2mm Sub Units – Aluminum Interlocked Armor

AWG Size	Fiber Count	Part Number ¹	Jacket Color	Nom. Jacket Dia. in (mm)	Weight lbs/1000ft (kg/km)	Max. Install Load lbs (N)	Max. Long Term Load lbs (N)
16	2	HIxB0020216CB	See Table	0.514 (13.1)	122 (182)	300 (1330)	90 (400)
18	2	HIxB0020218CB	See Table	0.504 (12.8)	114 (170)	300 (1330)	90 (400)
20	2	HIxB0020220CB	See Table	0.484 (12.3)	107 (159)	300 (1330)	90 (400)
1 Substitute (x) with Fiber Grade Code							



STANDARD															
FX Fiber Cable		Fiber Type		Family		Fiber Count		Conductor Count		Copper Type		Flammability		Subunit Type / Configuration	
HD		3		B		002		02		12		R		B	
HI	IndoorHybrid Cable	3	OM3	B	Breakout	001	1 Fiber	01	1 Conductor	12	12 AWG	L	LSZH (CMR-OF / CL3R-OF)	B	COPPER: Stranded or Category Cable FIBER: 2.0mm Sub, 1 x 900um Fiber / Sub
		4	OM4			002	2 Fibers	02	2 Conductors	14	14 AWG	C	LSZH Interlocked Aluminum Armor (OFCR)	C	COPPER: Stranded or Category Cable FIBER: 3.0mm Sub, 1 x 900um Fiber / Sub
		S	OS2 (G.657.A1)							16	16 AWG				
										18	18 AWG				
										20	20 AWG				