



Product: [127903A](#)

DataTuff® 5e, 4Pr #22 Sol BC, PO Ins, OS, PVC Jkt, AIA Armor, PVC Jkt, PLTC CMR

Product Description

Industrial Ethernet Cat 5e, 4 Pair 22AWG (Solid) Bare Copper, PO Insulation, Overall Beldfoil® Shield, PVC Inner Jacket, Aluminum Interlock Armor, PVC Outer Jacket, PLTC CMR

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, IP cameras and devices, data communication, etc. exposure to rodent, crush, or cut through force, power-limited tray.
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	Solid	BC - Bare Copper	0.026 in	4

Conductor Count:	8
Total Number of Pairs:	4

Insulation

Material
PO - Polyolefin

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Inner Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.335 in	0.043 in

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.655 in	0.045 in

Construction and Dimensions

Armor

Type of Armor	Material	Diameter over Armoring
Interlocked Armor	Aluminum	0.565 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR

9 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor

15 pF/ft

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
1 MHz	2 dB/100m
4 MHz	4.1 dB/100m
8 MHz	5.8 dB/100m
10 MHz	6.5 dB/100m
16 MHz	8.2 dB/100m
20 MHz	9.3 dB/100m
25 MHz	10.4 dB/100m
31.25 MHz	11.7 dB/100m
62.5 MHz	17 dB/100m
100 MHz	22 dB/100m
	28.1 dB/100m
	32 dB/100m
	36.9 dB/100m
	41.0 dB/100m
	41.8 dB/100m
	44.9 dB/100m

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

Installation Temp Range:	-25°C To +75°C
UL Temp Rating:	75°C
Storage Temp Range:	-25°C To +75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Oil Resistance:	Yes
UV Resistance:	Yes
Max. Pull Tension:	200 lbs
Min Bend Radius/Minor Axis:	7.86 in

Standards

NEC/(UL) Compliance:	CMR, PLTC
CEC/C(UL) Compliance:	CMR
Data Category:	Category 5e

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-04

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL 1666 Riser
CSA Flammability:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	UPC
127903A 0101000	612825439073
127903A 0105000	612825439080

History

Update and Revision:	Revision Number: 0.34 Revision Date: 09-30-2020
----------------------	---

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.