



Product Lens

a materials health assessment

COMPANY AND PRODUCT INFO

Issued to	Belden
Description	High Strand Speaker Cable, Non-Plenum Stranded Bare Copper Conductors, 10 to 18 AWG 2 to 4 Conductors, Unshielded
For the Products	5T00UPxxx, 5000UPxxx, 5002UPxxx, 5100UPxxx, 5102UPxxx, 5200UPxxx, 5202UPxxx, 5300UPxxx
Certification Period	March 2017- March 2019
Assessor	MBDC basis methodology v3.1*



Qualifications

- LEED BPDO Credit: Material Ingredients Option 1 Qualifies for as 1 product
- LEED BPDO Credit: Material Ingredients Option 2 Qualifies for 100% of cost

Other Achievements



MATERIALS / INGREDIENTS INFORMATION

Disclosure Level: 100 ppm 1000 ppm

The following table represents the top 90% of the material ingredient disclosure and ratings. For the full ingredient disclosure information, please see the table on the reverse side.

Materials	Result			
	Supply Chain/ MFG	Install	Use	End of Use
Copper	Yellow	Green	Green	Yellow
PVC	Red (I,D)	Yellow	Yellow	Red (I,D)
Plasticizer	Green	Green	Green	Green
Filler	Green	Green	Green	Green
Plasticizer	Black	Black	Black	Black
Proprietary	Grey	Grey	Grey	Grey
Plasticizer	Green	Green	Green	Green
Plasticizer	Green	Green	Green	Green

Exposure Indicator

D = Dermal, Skin
I = Inhalation, air
O = Oral, mouth

*No Indicator means no potential exposure scenario identified

Color Ratings

Green	Low or mild hazard identified and/or potential exposure
Yellow	Moderate hazard identified and/or potential exposure
Red	Problematic concern found. The combination of the hazard and potential exposure leads to some caution for some uses and/or applications.
Grey	Cannot be fully assessed due to either lack of complete formulation, or lack of toxicological information for one or more ingredients.
Black	Highly problematic material containing one or more chemicals classified as CMR and having a plausible route of exposure.

Go to ul.com/spg to view the full, detailed materials ingredient list

www.belden.com

Sustainability@belden.com

1-800-BELDEN1



*Methodology based on Cradle to Cradle Certified™ Product Material Health Assessment Methodology v3.1

Declaration Number: 4787608281.304.1



CERTIFIED

PRODUCT LENS MATERIALS
TRANSPARENCY AND
DISCLOSURE.
VIEW SPECIFIC INGREDIENTS
AND EVALUATIONS:
UL.COM/PL

Product Lens

a materials health assessment

Material	CAS Number	Role	%					Comment
				MFG	Install	Use	End of Use	
Copper	7440-50-8	Conductor	62-73					Highly toxic to aquatic organisms; however, this material is acceptable for use in all phases due to limited exposure opportunity to biosphere
PVC	9002-86-2	Jacket/ Colorant	14-18	I,D			I,D	Lifecycle concerns around use of halogenated polymers.
Plasticizer	Proprietary	Insulation	3.0-5.0					Little to no risk across all product phases
Filler	Proprietary	Various components	3.5-4.0					Little to no risk across all product phases
Plasticizer	Proprietary	Jacket	3.0-3.3					CMR - Reproductive toxin (CA Prop 65)
Proprietary	Unknown	Insulation Ingredient	0.3-0.8					Unknown
Plasticizer	Proprietary	Jacket	0.7-0.9					Little to no risk across all product phases
Plasticizer	Proprietary	Jacket	0.6-0.8					Little to no risk across all product phases
Flame Retardant	Proprietary	Jacket/ Insulation	0.5-1.0					Suspected human carcinogen (CA Prop 65, IARC Group 2B, MAK Group 2)
Titanium Dioxide	13463-67-7	Various components	0.2-0.3					Little to no risk across all product phases
Proprietary	Proprietary	Various colorants	0.15-0.20					CMR - suspected endocrine disruptor and potential reproductive toxicant (CA Prop 65)
Proprietary	Proprietary	Jacket	0.09-0.12					Little to no risk across all product phases
Proprietary	Proprietary	Colorant	0.10-0.15					Little to no risk across all product phases
PET	25038-59-9	Binder/Ripcord	0.09-0.12					Little to no risk across all product phases
Proprietary	Proprietary	Processing Aid	0.09-0.12					Little to no risk across all product phases
Proprietary	Proprietary	Insulation	<0.1					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05	D				Skin sensitization and aquatic toxicity concerns, however, at this concentration and in this use should be acceptable across all phases.
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.05					Little to no risk across all product phases
Proprietary	Proprietary	Jacket	<0.01					Little to no risk across all product phases
Polyethylene	9002-88-4	Jacket Colorant	<0.01					Little to no risk across all product phases
Proprietary	Proprietary	Colorant	<0.01					Little to no risk across all product phases
Proprietary	Proprietary	Colorant	<0.01					Little to no risk across all product phases

	Low or mild hazard identified and/or potential exposure
	Moderate hazard identified and/or potential exposure
	Problematic concern found. The combination of the hazard and potential exposure leads to some caution for some uses and/or applications.
	Cannot be fully assessed due to either lack of complete formulation, or lack of toxicological information for one or more ingredients.
	Highly problematic material containing one or more chemicals classified as CMR and having a plausible route of exposure.

