

## 5000UH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information  
please call

1-800-Belden1



### General Description:

Security & Commercial Audio Cable, Riser-CL3R-FPLR 2-12 AWG stranded tinned copper conductors with polyolefin insulation, PVC jacket with ripcord

### Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems, Fire Alarm (For color Red only)(Dual Rated)

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	12	19x25	TC - Tinned Copper

Total Number of Conductors: 2

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PP - Polypropylene	0.011

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.017

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White

Overall Nominal Diameter: 0.260 in.

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 50 lbs/1000 ft.

Max. Recommended Pulling Tension: 152 lbs.

Min. Bend Radius/Minor Axis: 2.750 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL3R, FPLR

NEC Articles: 725 or 760

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

## 5000UH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

### Flame Test

UL Flame Test: UL1666 Vertical Riser

CSA Flame Test: FT4

### Suitability

Suitability - Indoor: Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 6000UH

### Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (µH/ft)

0.15

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

24.000

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

1.6

#### Max. Operating Voltage - UL:

Voltage

300 V RMS

#### Max. Recommended Current:

Description	Current
10C Temperature Rise	12 Amps per conductor @ 25°C ambient

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5000UH 0081000	1,000 FT	54.000 LB	GRAY		2 #12 PO FRPVC
5000UH 008500	500 FT	29.000 LB	GRAY		2 #12 PO FRPVC
5000UH 0101000	1,000 FT	54.000 LB	BLACK		2 #12 PO FRPVC

Revision Number: 0 Revision Date: 08-28-2015

© 2016 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).