

XFI44U2848-S003 NETWORK RACK 44RU/400U x 28w x 48d

- 82.125h x 28w x 48d
- WELDED STEEL FRAME CONSTRUCTION w/ REINFORCED CORNER POSTS
- HEAVY DUTY CASTERS
- HEAVY DUTY LEVELING LEGS
- COLOR: CARDINAL WHITE (C031-WH120) SEMI GLOSS TEXTURE

- (2) PAIR FULLY ADJUSTABLE AND REVERSIBLE EIA/OCP RAILS 44RU / 400U
- RAILS MOUNTED IN EIA CONFIGURATION
- SQUARE HOLE TYPE EIA SIDE FOR CAGE NUTS
- (50) M6 MOUNTING HARDWARE INCLUDED
- RAIL FINISH IS CLEAR ZINC PLATED
- NUMERICAL MARKINGS FOR EACH RACK UNIT w/ UNIT 1 STARTING @ BOTTOM

- FULL SIZE 78% PERFORATED CONTOUR FRONT & REAR DOOR
- LOCKING SWING HANDLE
- CONTOUR PERFORATED DOORS ADD 2.60 INCHES (PER DOOR) TO FRAME DEPTH DIMENSION



- (3)PC TOP PANEL
- FRONT w/ BRUSH FRAMES
- REAR w/ 5-1/4" DIA KNOCKOUTS & (2) GROMMETS
- CENTER PANEL IS SOLID

- PARTIAL BOTTOM PANEL w/ REAR CABLE OPENING

- FLUSH MOUNTED SIDE PANELS w/ TAMPER RESISTANT SCREWS

- (2) 3.5" VERTICAL PDU PANELS MOUNTED IN REAR
- (2) 2.0" VERTICAL LACING PANELS MOUNTED IN REAR
- (4) 6.0" VERTICAL LACING PANELS MOUNTED IN FRONT

- BOTTOM FRONT SKIRT



BELDEN

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED.

XFI44U2848-S003 / NETWORK RACK 44RU/400U x 28w x 48d

APPROVED BY: RCG DRAWING AUTHOR: RCG

APPROVAL DATE: 11/15/17

UNITS: INCH Sheet 1 of 1 D

SCALE: 1:8 DATE 11/15/2017

SUBMITTAL

REV	DESCRIPTION	BY	DATE