


XFI44U2848-S004 OPEN BRIDGE RACK 48RU/440U x 28w x 48d

- 89.125h x 28w x 48d
- WELDED STEEL FRAME CONSTRUCTION w/ REINFORCED CORNER POSTS
- HEAVY DUTY CASTERS
- HEAVY DUTY LEVELING LEGS
- COLOR: CARDINAL WHITE (C031-WH120) SEMI GLOSS TEXTURE
- (2) PAIR FULLY ADJUSTABLE AND REVERSIBLE EIA/OCP RAILS 48RU/440U
- RAILS MOUNTED IN OCP CONFIGURATION
- SQUARE HOLES TYPE EIA SIDE FOR CAGE NUT
- (50) M6 MOUNTING HARDWARE INCLUDED
- RAILS FINISH IS CLEAR ZINC PLATED
- NUMERICAL MARKINGS FOR EACH RACK UNIT w/ UNIT 1 STARTING @ BOTTOM
- FULL SIZE 78% PERFORATED CONTOUR FRONT & REAR DOOR
- LOCKING SWING HANDLE
- CONTOUR PERFORATED DOORS ADD 2.60 INCHES (PER DOOR) TO FRAME DEPTH DIMENSION
- (3)PC TOP PANEL
- FRONT & REAR PANELS HAVE 5-1/4IN DIA KNOCKOUTS
- CENTER PANEL IS SOLID
- ADDED (4) GROMMETS TO FRONT & REAR PANELS
- PARTIAL BOTTOM PANEL w/ REAR CABLE OPENING
- FLUSH MOUNTED SIDE PANELS w/ TAMPER RESISTANT SCREWS
- (2) VERTICAL LACING PANELS (OCP FRONT RAIL LOCATOR PANEL) MOUNTED IN FRONT
- (2) VERTICAL REAR LOCATION / POWER SHELF MOUNTING CHANNEL (OCP)
- BOTTOM FRONT SKIRT
- BOLT TOGETHER KIT w/ STRAP



BELDEN

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED.

OPEN BRIDGE RACK / XFI48U2848-S007

APPROVED BY: RCG DRAWING AUTHOR: RCG

APPROVAL DATE: 11/15/17

UNITS: INCH Sheet 1 of 1 D

SCALE: 1:8 DATE 11/15/2017

SUBMITTAL

REV	DESCRIPTION	BY	DATE