




Product information OZDV 2471 G-1300

Fiber Interfaces:LWL converter for serial signals:OZDV 2471 G-1300

<https://www.e-catalog.beldensolutions.com:443/link/57078-57141-57135-38306/en/conf/ui/state>

Name	OZDV 2471 G-1300
	
	interface converter electrical/optical for V.24; for quartz glass FO; for plugging onto the Sub-D socket provided on the terminal or mounting onto a DIN rail (with DIN rail adapter accessories); long-haul version
Delivery informations	
Availability	available
Product description	
Description	interface converter electrical/optical for V.24; for quartz glass FO; for plugging onto the Sub-D socket provided on the terminal or mounting onto a DIN rail (with DIN rail adapter accessories); long-haul version
Port type and quantity	1 electrical port: 25-pin Sub-D connector, male; 1 optical port: 2 sockets BFOC 2.5 (STR)
Setting possibilities	DTE- or DCE operating mode voltage supply internally via pin 11/pin 18 Sub-D socket or externally via low voltage socket shield ground galvanically connected or not connected to signal ground
Type	OZDV 2471 G-1300
Order No.	933 990-021
Electrical interface	
Signal type	V.24 (RS 232 D) interface level
Bit rate	DC to 115 kbit/s (DC coupling)
Bit error frequency	< 10 ⁻⁹
Terminal assignment data	pin 1: PGND; pin 7: GND; pin 11: Vcc; pin 4+5 and pin 6+8+20 bridged DTE operation: pin 2 TxD, pin 3 RxD DCE operation: pin 2 RxD, pin 3 TxD
Optical interface	
Wavelength	1300 nm
More Interfaces	
Power supply	4-pin low voltage plug, M8 shape according to IEC 947-5-2 or 25-pin Sub-D connector (pin 11/pin 18)
Network size - length of cable	
Single mode fiber (SM) 9/125 µm	0 - 32000 m 18 dB link budget, A = 0.5 dB/km, 2 dB reserve
Multimode fiber (MM) 50/125 µm	0 - 19000 m 21 dB link budget, A = 1.0 dB/km, 2 dB reserve
Multimode fiber (MM) 62.5/125 µm	0 - 12000 m 21 dB link budget, A = 1.5 dB/km, 2 dB reserve
Multimode fiber HCS (MM) 200/230 µm	-
Multimode fiber POF (MM) 980/1000 µm	-
Power requirements	
Operating voltage	+5 VDC via PSW 5-24 plug-in power supply or + 5 VDC +-5% external supply or +8 ... +15 VDC external supply
Current consumption	90 mA (max. 120 mA)
Power consumption	0.6 W/1.8 W
Ambient conditions	
Operating temperature	-20 °C to +50 °C
Storage/transport temperature	-20 °C to +70 °C



Fiber Interfaces:LWL converter for serial signals:OZDV 2471 G-1300

<https://www.e-catalog.beldensolutions.com:443/link/57078-57141-57135-38306/en/conf/ui/state>

Relative humidity	10% to 90%
Mechanical construction	
Dimensions (W x H x D)	56.5 x 18 x 80 mm
Mounting	plugging onto the terminal unit
Weight	135 g
Protection class	IP 40
Housing material	die-cast zink
Approvals	
Basis Standard	EC Conformity, RCM Conformity Australia
Scope of delivery and accessories	
Scope of delivery	device, operating instructions
Accessories to order separately	plug-in power supply PSW 5-24 DIN rail adapter OZDV HA

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.