

XFI48U2848-S006 NETWORK RACK 48RU/44OU x 28w x 48d

- 89.125h x 28w x 48d
- WELDED STEEL FRAME CONSTRUCTION w/ REINFORCED CORNER POSTS
- HEAVY DUTY CASTERS
- HEAVY DUTY LEVELING LEGS
- COLOR: CARDINAL WHITE (C031-WH120) SEMI GLOSS TEXTURE

- (2) PAIR FULLY ADJUSTABLE AND REVERSIBLE EIA/OCP RAILS 48RU / 44OU
- RAILS MOUNTED IN EIA CONFIGURATION
- SQUARE HOLE TYPE EIA SIDE FOR CAGE NUTS
- (50) M6 MOUNTING HARDWARE INCLUDED
- RAIL FINISH IS CLEAR ZINC PLATED
- NUMERICAL MARKINGS FOR EACH RACK UNIT w/ UNIT 1 STARTING @ BOTTOM

- FULL SIZE 78% PERFORATED CONTOUR FRONT & REAR DOOR
- LOCKING SWING HANDLE
- CONTOUR PERFORATED DOORS ADD 2.60 INCHES (PER DOOR) TO FRAME DEPTH DIMENSION



- (3)PC TOP PANEL
- FRONT w/ BRUSH FRAMES
- REAR w/ 5-1/4" DIA KNOCKOUTS & (2) GROMMETS
- CENTER PANEL IS SOLID

- PARTIAL BOTTOM PANEL w/ REAR CABLE OPENING

- FLUSH MOUNTED SIDE PANELS w/ TAMPER RESISTANT SCREWS

- (2) 3.5" VERTICAL PDU PANELS MOUNTED IN REAR
- (2) 2.0" VERTICAL LACING PANELS MOUNTED IN REAR
- (4) 6.0" VERTICAL LACING PANELS MOUNTED IN FRONT

- BOTTOM FRONT SKIRT



**BELDEN**

THIS DRAWING AND ALL INFORMATION CONTAINED HEREIN IS THE PROPERTY OF BELDEN. ANY USE, COPY OR REPRODUCTION OF THIS MATERIAL WITHOUT WRITTEN PERMISSION OF BELDEN IS PROHIBITED.

XFI48U2848-S006 / NETWORK RACK 48RU/44OU x 28w x 48d

APPROVED BY: RCG DRAWING AUTHOR: RCG

APPROVAL DATE: 11/15/17

UNITS: INCH Sheet 1 of 1 D

SCALE: 1:8 DATE 11/15/2017 SUBMITTAL

| REV | DESCRIPTION | BY | DATE |
|-----|-------------|----|------|
|     |             |    |      |