



## Product information Managed Fast Ethernet Power Rail Switches - Smart - RSPS25-06002T1TTSCCZ9HDE2S06.0.

Industrial Ethernet:Power Rail Switches:RSPS - Smart Switches:with HiOS 6.0:Managed Fast Ethernet Power Rail Switches - Smart

<https://e-catalog.beldensolutions.com:443/link/57078-24455-202442-279207-460721-460722/en/RSPS25-06002T1TTSCCZ9HDE2S06.0/uistate>

<b>Name</b>		Managed Fast Ethernet Power Rail Switches - Smart
		
		Managed, Industrial Switch DIN Rail, fanless design. Fast Ethernet type, enhanced Redundancy (PRP, Fast MRP, HSR*).
<b>Delivery informations</b>		
<b>Availability</b>	available	
<b>Product description</b>		
<b>Description</b>	Managed, Industrial Switch DIN Rail, fanless design. Fast Ethernet type, enhanced Redundancy (PRP, Fast MRP, HSR*).	
<b>Port type and quantity</b>	6 Ports in total, 6 x (10/100Mbit/s) Twisted Pair / RJ45	
<b>Type</b>	RSPS25-06002T1TTSCCZ9HDE2S06.0.	
<b>Order No.</b>	RSPS25-06002T1TTSCCZ9HDE2S06.0.	
<b>More Interfaces</b>		
<b>Power supply/signaling contact</b>	2 x plug-in terminal block, 2-pin, 1 x plug-in terminal block, 2-pin	
<b>V.24 interface</b>	1 x RJ11 socket	
<b>SD-card slot</b>	1 x SD card slot to connect the auto configuration adapter ACA31	
<b>Network size - length of cable</b>		
<b>Twisted pair (TP)</b>	0 m ... 100 m	
<b>Multimode fiber (MM) 50/125 µm</b>	see SFP Fiber Module M-Fast SFP-xx	
<b>Multimode fiber (MM) 62.5/125 µm</b>	see SFP Fiber Module M-Fast SFP-xx	
<b>Single mode fiber (SM) 9/125 µm</b>	see SFP Fiber Module M-Fast SFP-xx	
<b>Single mode fiber (LH) 9/125 µm (long haul transceiver)</b>	see SFP Fiber Module M-Fast SFP-xx	
<b>Network size - cascability</b>		
<b>Line - / star topology</b>	any	
<b>Ring structure (HIPER-Ring) quantity switches</b>	MRP, RSTP	
<b>Power requirements</b>		
<b>Operating voltage</b>	2 x 24/36/48 VDC (18-60 VDC)	
<b>Power consumption</b>	12 W	
<b>Power output in Btu (IT) h</b>	40	
<b>Software</b>		
<b>Management</b>	TFTP; SFTP; SCP; LLDP (802.1AB); LLDP-MED; SSHv2; V.24; HTTP; HTTPS; Traps; SNMP v1/v2/v3; Telnet	
<b>Configuration</b>	Automatic Configuration Undo (roll-back); Configuration Fingerprint; Text-based Configuration File (XML); BOOTP/DHCP Client with Auto-Configuration; DHCP Server: per Port; DHCP Server: Pools per VLAN; AutoConfiguration Adapter ACA31 (SD card); HiDiscovery; Command Line Interface (CLI); CLI Scripting; Full-featured MIB Support; Web-based Management; Context-sensitive Help	
<b>Security</b>	MAC-based Port Security; Port-based Access Control with 802.1X; Guest/unauthenticated VLAN; Integrated Authentication Server (IAS); RADIUS VLAN Assignment; Automatic Denial-of-Service Prevention; Access to Management restricted by VLAN; Device Security Indication; Audit Trail; CLI Logging; HTTPS Certificate Management; Restricted Management Access; Appropriate Use Banner; Configurable Password Policy; Configurable Number of Login Attempts; SNMP Logging; Multiple Privilege Levels; Local User Management; Remote Authentication via RADIUS; User Account Locking	
<b>Redundancy functions</b>	Device Level Ring (DLR); Link Aggregation with LACP; Link Backup; Media Redundancy Protocol (MRP) (IEC62439-2); Fast MRP (IEC62439-2); High Availability Seamless Redundancy Protocol (HSR) (IEC62439-3); Parallel Redundancy Protocol (PRP) (IEC62439-3); RSTP 802.1D-2004 (IEC62439-1); RSTP Guards	
<b>Time synchronisation</b>	PTPv2 Transparent Clock two-step; PTPv2 Boundary Clock; Buffered Real Time Clock; SNTP Client; SNTP Server	
<b>Miscellaneous</b>	Manual Cable Crossing, Port Power Down	
<b>Switching</b>	Independent VLAN Learning; Fast Aging; Static Unicast/Multicast Address Entries; QoS / Port Prioritization (802.1D/p); TOS/DSCP Prioritization; Interface Trust Mode; CoS Queue Management; Flow Control (802.3X); Egress Interface Shaping; Ingress Storm Protection; VLAN (802.1Q); VLAN Unaware Mode; Voice VLAN; IGMP Snooping/Querier per VLAN (v1/v2/v3); Unknown Multicast Filtering; Multiple VLAN Registration Protocol (MVRP); Multiple MAC Registration Protocol (MMRP); Multiple Registration Protocol (MRP)	



## Industrial Ethernet:Power Rail Switches:RSPS - Smart Switches:with HiOS 6.0:Managed Fast Ethernet Power Rail Switches - Smart

<https://e-catalog.beldensolutions.com:443/link/57078-24455-202442-279207-460721-460722/en/RSPS25-06002T1TTSCCZ9HDE2S06.0./uistate>

### Ambient conditions

Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 70 °C
Relative humidity (non-condensing)	10 % ... 95 %

### Mechanical construction

Dimensions (W x H x D)	90 mm x 164 mm x 120 mm
Mounting	DIN Rail
Weight	1180 g
Protection class	IP30

### Mechanical stability

IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min

### EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD)	8 kV contact discharge, 15 kV air discharge
EN 61000-4-3 electromagnetic field	35 V/m (80-2700 MHz); 1 kHz, 80% AM
EN 61000-4-4 fast transients (burst)	4 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line, IEEE1613: power line 5 kV (line/earth)
EN 61000-4-6 conducted immunity	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
EN 61000-4-16 mains frequency voltage	30 V, 50 Hz continuous; 300 V, 50 Hz 1 s

### EMC emitted immunity

FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A

### Approvals

Basis Standard	CE, FCC, EN61131
----------------	------------------

### Scope of delivery and accessories

Scope of delivery	Device, terminal block, operating manual
-------------------	--

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.