

1384LP Multi-Conductor - Commercial AV, Automation/Lighting Control Cable



For more Information
please call

1-800-Belden1



General Description:

Lighting & Automation Cable, Plenum-CMP, 5-22 AWG solid bare copper conductors with FEP insulation, Beldfoil® shield and FEP jacket

Usage (Overall)

Suitable Applications: Automation/Lighting Control

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
5	22	SOLID	Bare High-Conductivity ETP Copper

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Outer Shield Material	Coverage (%)
Beldfoil®	Aluminum Foil-Polyester Tape	100.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	Solid	TC - Tinned Coppe

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Cabling Color Code Chart:

Color
Black
Red
White
Yellow
Blue

Overall Nominal Diameter: 0.137 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-55°C To +200°C
Bulk Cable Weight:	17 lbs/1000 ft.
Max. Recommended Pulling Tension:	46 lbs.
Min. Bend Radius/Minor Axis:	1.500 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CL3P
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes

1384LP Multi-Conductor - Commercial AV, Automation/Lighting Control Cable

EU RoHS Compliance Date (mm/dd/yyyy):	05/07/12
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL910 Plenum
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Plenum Number:	1384LA

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
17.000

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
16.100

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
3.8 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1384LP 3681000	1,000 FT	19.000 LB	CLEAR, TRANSPARENT		5 #22 FEP FS FEP

Revision Number: 1 Revision Date: 05-23-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).