


1700R Multi-Conductor - Enhanced Category 5E Bonded-Pair Cable



No longer Available
1-800-BELDEN1

For more Information
please call

1-800-Belden1



General Description:

CAT5e+ (350MHz), 4-Bonded-Pairs, U/UTP-Unshielded, Riser-CMR, Premise Horizontal Cable, 24 AWG Solid Bare Copper Conductors, Polyolefin Insulation, Ripcord, PVC jacket.

Usage (Overall)

Suitable Applications: Premise Horizontal Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.202

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.202 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

Bulk Cable Weight: 21 lbs/1000 ft.

Max. Recommended Pulling Tension: 40 lbs.

Min. Bend Radius/Minor Axis: 1 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMR

CEC/C(UL) Specification: CMR

EU Directive 2011/65/EU (ROHS II): Yes

1700R Multi-Conductor - Enhanced Category 5E Bonded-Pair Cable

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Applicable Patents:

Country
www.belden.com/p

Flame Test

UL Flame Test:	UL1666 Riser
C(UL) Flame Test:	FT4
IEC Flame Test:	60332-3-22 (Category A)
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1701A

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)
15

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
510

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. PSNEXT (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.000	68.3	66.3	20.000
4	4.000	59.3	55.3	23.000
8	5.700	54.8	49.1	24.500
10	6.400	53.3	46.9	25.000
16	8.100	50.3	42.2	25.000
20	9.100	48.8	39.7	25.000
25	10.200	47.3	37.1	25.000

1700R Multi-Conductor - Enhanced Category 5E Bonded-Pair Cable

31.25	11.400	45.9	34.5	25.000
62.5	16.400	41.4	25.0	25.000
100	21.000	38.3	17.3	25.000
155	26.600	35.4	8.8	19.000
200	30.500	33.8	3.3	19.000
250	34.300	32.3	>0	18.000
300	38.000	28.2		18.000
350	41.400	27.2		17.000

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. PSACRF (dB)
1	100 ± 12	105 ± 10	64.8
4	100 ± 12	100 ± 10	52.8
8	100 ± 12	100 ± 10	46.7
10	100 ± 12	100 ± 10	44.8
16	100 ± 12	100 ± 10	40.7
20	100 ± 12	100 ± 10	38.8
25	100 ± 15	100 ± 10	36.8
31.25	100 ± 15	100 ± 10	34.9
62.5	100 ± 15	100 ± 10	28.9
100	100 ± 15	100 ± 10	24.8
155	100 ± 18	100 ± 10	21.0
200	100 ± 20	100 ± 10	18.8
250	100 ± 20	100 ± 10	16.8
300	100 ± 20	100 ± 10	11.2
350	100 ± 22	100 ± 10	9.9

Premise Cable Electrical Table 4:

Frequency (MHz)	Min. TCL (dB)	Min. ELTCTL (dB)
1.000	40.000	35.000
4.000	40.000	23.000
8.000	40.000	16.900
10.000	40.000	15.000
16.000	38.000	10.900
20.000	37.000	9.000
25.000	36.000	7.000
31.250	35.100	
62.500	32.000	
100.000	30.000	
155.000	28.100	
200.000	27.000	
250.000	26.000	

Notes (Overall)

Notes: Belden IBDN. Jacket sequentially marked at 2 ft. intervals. U.S. Patents 5424491 and 5734126. Third party verified to TIA/EIA-568-C.2, Category 5e.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 7 Revision Date: 02-28-2014

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).