




## Product information Compact OpenRail Gigabit Ethernet PoE switch 8-24 ports - RS32-16020606SPAEHF09.0.

Industrial Ethernet: Compact configurable managed switches: with Classic Software 9.0: Compact OpenRail Gigabit Ethernet PoE switch 8-24 ports

<https://e-catalog.beldensolutions.com:443/link/57078-24455-49854-458702-458699/en/RS32-16020606SPAEHF09.0/uistate>

<b>Name</b>	Compact OpenRail Gigabit Ethernet PoE switch 8-24 ports
	
	18 port Gigabit/fast Ethernet switch (2 x Gigabit Ethernet, 16 x fast Ethernet from that 4 ports PoE), managed, software Layer 2 Enhanced, for DIN rail, store-and-forward-switching, fanless design, metal housing
<b>Delivery informations</b>	
<b>Availability</b>	available
<b>Product description</b>	
<b>Description</b>	18 port Gigabit/fast Ethernet switch (2 x Gigabit Ethernet, 16 x fast Ethernet from that 4 ports PoE), managed, software Layer 2 Enhanced, for DIN rail, store-and-forward-switching, fanless design, metal housing
<b>Port type and quantity</b>	18 Ports in total, 2 Gigabit Ethernet ports; 1. uplink: Gigabit SFP-Slot; 2. uplink: Gigabit SFP-Slot; 16 x standard 10/100 BASE TX, RJ45 incl. 4 PoE Ports
<b>Type</b>	RS32-16020606SPAEHF09.0.
<b>Order No.</b>	RS32-16020606SPAEHF09.0.
<b>More Interfaces</b>	
<b>Power supply/signaling contact</b>	1 x plug-in terminal block, 6-pin
<b>V.24 interface</b>	1 x RJ11 socket
<b>USB interface</b>	1 x USB to connect the AutoConfiguration Adapter ACA21-USB
<b>Network size - length of cable</b>	
<b>Multimode fiber (MM) 50/125 µm</b>	cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
<b>Multimode fiber (MM) 62.5/125 µm</b>	cf. SFP LWL module M-SFP-SX/LC and M-SFP-LX/LC
<b>Single mode fiber (SM) 9/125 µm</b>	cf. SFP LWL module M-SFP-LX/LC
<b>Single mode fiber (LH) 9/125 µm (long haul transceiver)</b>	cf. SFP LWL module M-SFP-LH/LC and M-SFP-LH+/LC
<b>Network size - cascading</b>	
<b>Line - / star topology</b>	any
<b>Ring structure (HIPER-Ring) quantity switches</b>	50 (reconfiguration time < 0.3 sec.)
<b>Power requirements</b>	
<b>Operating voltage</b>	48 V DC
<b>Current consumption at 48 V DC</b>	156 mA
<b>Power output in Btu (IT) h</b>	52.6
<b>Software</b>	
<b>Management</b>	TFTP; LLDP (802.1AB); V.24; HTTP; Traps; SNMP v1/v2/v3; Telnet
<b>Diagnostics</b>	Management Address Conflict Detection; Address Relearn Detection; Signal Contact; Device Status Indication; LEDs; Syslog; Duplex Mismatch Detection; RMON (1,2,3,9); Port Mirroring 1:1; Port Mirroring 8:1; System Information; Self-Tests on Cold Start; SFP Management; Switch Dump
<b>Configuration</b>	AutoConfiguration Adapter ACA11 Limited Support (RS20/30/40, MS20/30); Automatic Configuration Undo (roll-back); Configuration Fingerprint; BOOTP/DHCP Client with Auto-Configuration; AutoConfiguration Adapter ACA21/22 (USB); HiDiscovery; DHCP Relay with Option 82; Command Line Interface (CLI); Full-featured MIB Support; Web-based Management; Context-sensitive Help
<b>Security</b>	IP-based Port Security; MAC-based Port Security; Access to Management restricted by VLAN; SNMP Logging; Local User Management
<b>Redundancy functions</b>	HIPER-Ring (Manager); HIPER-Ring (Ring Switch); Media Redundancy Protocol (MRP) (IEC62439-2); Redundant Network Coupling; RSTP 802.1D-2004 (IEC62439-1); RSTP Guards; RSTP over MRP
<b>Industrial Profiles</b>	EtherNet/IP Protocol; PROFINET IO Protocol
<b>Time synchronisation</b>	SNTP server and client
<b>Miscellaneous</b>	PoE (802.3AF); Manual Cable Crossing
<b>Switching</b>	Disable Learning (hub functionality); Independent VLAN Learning; Fast Aging; Static Unicast/Multicast Address Entries; QoS / Port Prioritization (802.1D/p); TOS/DSCP Prioritization; Egress Broadcast Limiter per Port; Flow Control (802.3X); VLAN (802.1Q); IGMP Snooping/Querier (v1/v2/v3)
<b>Ambient conditions</b>	
<b>Operating temperature</b>	0 °C ... 60 °C



## Industrial Ethernet: Compact configurable managed switches: with Classic Software 9.0: Compact OpenRail Gigabit Ethernet PoE switch 8-24 ports

<https://e-catalog.beldensolutions.com:443/link/57078-24455-49854-458702-458699/en/RS32-16020606SPAEHF09.0/ui/state>

<b>Storage/transport temperature</b>	-40 °C ... 70 °C
<b>Relative humidity (non-condensing)</b>	10 % ... 95 %
<b>MTBF</b>	19.2 years (MIL-HDBK-217F)
<b>Protective paint on PCB</b>	No
<b>Mechanical construction</b>	
<b>Dimensions (W x H x D)</b>	120 mm x 137 mm x 115 mm
<b>Mounting</b>	DIN Rail
<b>Weight</b>	1150 g
<b>Protection class</b>	IP20
<b>Mechanical stability</b>	
<b>IEC 60068-2-27 shock</b>	15 g, 11 ms duration, 18 shocks
<b>IEC 60068-2-6 vibration</b>	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
<b>EMC interference immunity</b>	
<b>EN 61000-4-2 electrostatic discharge (ESD)</b>	6 kV contact discharge, 8 kV air discharge
<b>EN 61000-4-3 electromagnetic field</b>	10 V/m (80-1000 MHz)
<b>EN 61000-4-4 fast transients (burst)</b>	2 kV power line, 1 kV data line
<b>EN 61000-4-5 surge voltage</b>	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
<b>EN 61000-4-6 conducted immunity</b>	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
<b>EMC emitted immunity</b>	
<b>FCC CFR47 Part 15</b>	FCC 47 CFR Part 15 Class A
<b>EN 55022</b>	EN 55022 Class A
<b>Approvals</b>	
<b>Safety of industrial control equipment</b>	cUL 508
<b>Hazardous locations</b>	ISA 12.12.01 Class 1 Div. 2 (pending)
<b>Shipbuilding</b>	n/a
<b>Railway norm</b>	n/a
<b>Substation</b>	n/a
<b>Scope of delivery and accessories</b>	
<b>Scope of delivery</b>	Device, terminal block, operating manual

For more information please contact:

**Hirschmann Automation and Control GmbH**

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: [inet-sales@belden.com](mailto:inet-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.