

## AX104623 Faceplates and Panels - KeyConnect Shielded Angled Patch Panel, 48-port, 2U, Titanium (Empty)



For more Information  
please call

1-800-Belden1



### General Description:

KeyConnect Shielded Angled Patch Panel, 48-port, 2U, Titanium (Empty)

### Usage (Overall)

|                               |  |
|-------------------------------|--|
| <b>Suitable Applications:</b> | - Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200. |
| <b>Related Parts:</b>         | - Compatible with Shielded 10GX, CAT6 and CAT5E KeyConnect Modular Jacks   |

### Physical Characteristics (Connectivity)

#### Capacity

|                       |               |
|-----------------------|---------------|
| <b>Max. Capacity:</b> | 48 connectors |
|-----------------------|---------------|

#### Access

|                          |       |
|--------------------------|-------|
| <b>Front Connection:</b> | Flush |
| <b>Termination Area:</b> | Rear  |

#### Dimensions

Dimensions:

| Height (in.) | Width (in.) | Depth (in.) |
|--------------|-------------|-------------|
| 3.470        | 19.000      | 11.540      |

#### Materials

Materials:

| Description | Material |
|-------------|----------|
| Panel       | Steel    |

#### Color

|               |          |
|---------------|----------|
| <b>Color:</b> | Titanium |
|---------------|----------|

#### Weight

|                |            |
|----------------|------------|
| <b>Weight:</b> | 3.900 lbs. |
|----------------|------------|

#### Included Parts

|                        |   |
|------------------------|---|
| <b>Included Parts:</b> | 4 Screws (10x32); 4 Screws (12x24); 1 Printable Label Holder; 2 Velcro Straps; 2 Rear Cable Management Bracket/Bar, 1 Installation Guide, Ground Wire 12AWG Kit |
|------------------------|---|

#### Packaging

|                   |   |
|-------------------|---|
| <b>Packaging:</b> | Individually packaged in a cardboard box. |
|-------------------|---|

### Mechanical Characteristics (Connectivity)

|  |                |
|--|----------------|
| <b>Storage Temperature Range:</b>      | -40°C To +70°C |
| <b>Installation Temperature Range:</b> | -10°C To +60°C |
| <b>Operating Temperature Range:</b>    | -10°C To +60°C |

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

|  |   |
|--|---|
| <b>EU Directive 2002/95/EC (RoHS):</b>       | Yes   |
| <b>EU RoHS Compliance Date (mm/dd/yyyy):</b> | 01/10/2008  |
| <b>MIL Order #39 (China RoHS):</b>           | Yes   |
| <b>Telecommunications Standards:</b>         | Category 5e - TIA 568.C.2, Category 6 - TIA 568.C.2, Category 6A - TIA 568.C.2, Class E - ISO/IEC 11801:2002, Class EA - ISO/IEC 11801:2002 Amendment 2, Class D - ISO/IEC 11801:2002 |
| <b>Safety Listing:</b>                       | Bi-national Standard Listed   |

#### Suitability

|                              |     |
|------------------------------|-----|
| <b>Suitability - Indoor:</b> | Yes |
|------------------------------|-----|

## ENGLISH MEASUREMENT VERSION

### AX104623 Faceplates and Panels - KeyConnect Shielded Angled Patch Panel, 48-port, 2U, Titanium (Empty)

#### Transmission Characteristics (Connectivity)

#### Notes (Overall)

**Notes:** For proper installation refer to Installation Guide PX105408 included with the product or visit our web site at <http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf>

#### Product Family

#### Put Ups and Colors:

| Item #   | Putup | Ship Weight | Color | Notes | Item Desc                      |
|----------|-------|-------------|-------|-------|--------------------------------|
| AX104623 | 1 EA  | 3.339 LB    |       |       | KCONN SHD ANGLED PPANEL 48P 2U |

Revision Number: 0    Revision Date: 12-03-2012

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.