

1269A Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable



For more Information
please call

1-800-Belden1



General Description:

22 AWG solid TC conductors, plenum, solid FEP insulation, twisted pairs, overall Beldfoil (100% coverage) + TC braid shield (90% coverage), 22 AWG solid TC drain wire, FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	22	Solid	TC - Tinned Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
Solid FEP - Solid Fluorinated Ethylene Propylene	0.406

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	90

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
22	Solid		TC - Tinned Copper

Outer Shield Separator Material: Polyester Tape

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
FEP - Fluorinated Ethylene Propylene	0.432

Overall Cable

Overall Nominal Diameter: 6.096 mm

Pair

Pair Color Code Chart:

Number	Color
1	Red & Blue
2	Black & Yellow

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Bulk Cable Weight: 65.481 Kg/Km

Max. Recommended Pulling Tension: 391.442 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP, MPP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

METRIC MEASUREMENT VERSION

1269A Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	1268A

Surface Printing (Overall)

Surface Printing:	BELDEN-E 1269A E108998 2PR22 200C SHIELDED (UL) CMP C(UL)
-------------------	---

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	100
-----------------	-----

Nom. Inductance:

Inductance (µH/m)	0.55777
-------------------	---------

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)	50.8555
--------------------	---------

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)	88.587
--------------------	--------

Nominal Velocity of Propagation:

VP (%)	69.5
--------	------

Nominal Delay:

Delay (ns/m)	4.79026
--------------	---------

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)	54.1365
---------------------	---------

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)	6.8901
---------------------	--------

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
.3	1.3124
.6	1.73893
1.0	2.13265
1.5	2.55918

Max. Operating Voltage - UL:

Voltage	300 V RMS
---------	-----------

Max. Recommended Current:

Current	2.3 Amps per conductor @ 25°C
---------	-------------------------------

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1269A 0101000	1,000 FT	48.000 LB	BLACK	C	2 PR #22 FEP SH FEP

Notes:
C = CRATE REEL PUT-UP.

METRIC MEASUREMENT VERSION

1269A Multi-Conductor - Low Capacitance Computer and Computer P.O.S. Cable

Revision Number: 2 Revision Date: 11-09-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).