


6100FH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information
please call

1-800-Belden1



General Description:

Security & Commercial Audio Cable, Plenum-CL2P, 2-14 AWG stranded tinned copper conductors with Flamarrest® insulation, Beldfoil® shield and Flamarrest® jacket with ripcord

Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	14	19x27	TC - Tinned Copper

Total Number of Conductors: 2

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.279

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	Solid	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (mm)
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride	0.381

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White

Overall Nominal Diameter: 5.842 mm

Mechanical Characteristics (Overall)

Bulk Cable Weight: 68.457 Kg/Km

Max. Recommended Pulling Tension: 557.804 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CL2P

NEC Articles: 725

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU Directive 2002/96/EC (WEEE): Yes

METRIC MEASUREMENT VERSION

6100FH Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Flame Test	
UL Flame Test:	NFPA 262
Suitability	
Suitability - Indoor:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	Yes
Non-Plenum Number:	5100FH

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.475745

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
278.885

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
501.993

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
8.33374

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
32.810

Max. Operating Voltage - UL:

Voltage
150 V RMS

Max. Recommended Current:

Description	Current
10C Temperature Rise	8 Amps per conductor @ 25°C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
6100FH 8771000	1,000 FT	43.000 LB	NATURAL		2 #14 FLRST FS FLRST

Revision Number: 0 Revision Date: 08-28-2015

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).