

CAPFMUS-S1 Modular Connectors - FIELD MOUNT PLUG CAT6A UTP, SMALL AWG 24-26



For more Information
please call

1-800-Belden1



General Description:

CATEGORY 6A FIELD MOUNT PLUG, 568A/B, UTP, SMALL AWG 24-26 (0.033 - 0.042 IN.)

Usage (Overall)

Suitable Applications: Up to TIA Category 6A, ISO Class EA, 10Base-TX, 100Base-TX, 1000Base-T, 10GBase-T and IBDN Systems

Related Parts: Recommended CAT5E, CAT6 and CAT6A UTP cables (Solid & Stranded).

Physical Characteristics (Connectivity)

Dimensions

Dimensions:

Height (in.)	Width (in.)	Length (in.)
0.650	0.540	1.750

Materials

Materials:

Description	Type	Material	Color
Connector housing		Polycarbonate - UL94V-0	Black
Contact housing	RJ45	Polycarbonate - UL94V-0	Clear
Contacts		Phosphor Bronze Alloy Plated with 50u inch Gold	
PCB		FR4 UL94V-0	

Wiring Scheme

Wiring Scheme: T568A and T568B

Weight

Weight: 0.028 lbs.

Included Parts

Included Parts: RJ45 Connector, Wire Manager, Installation Guide.

Packaging

Packaging: Individually packaged in a clear plastic bag.

Mechanical Characteristics (Connectivity)

Termination Interface:

Termination	Connection	Durabilities
RJ45	Mated Connection	750 Cycles

Operating Temperature Range: -40°C To +70°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

Other Standards: FCC Part 68, Subpart F, IEC 60603-7

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

Telecommunications Standards: Category 6A - TIA 568.C.2, ISO/IEC 11801:2002 Ed.2

Other Specification: Complies with ANSI/TIA-1096-A Requirements.

Flame Test

UL Flame Test: UL2043 Air Handling Spaces

Suitability

CAPFMUS-S1 Modular Connectors - FIELD MOUNT PLUG CAT6A UTP, SMALL AWG 24-26

Suitability - Indoor: Yes - Indoor

Transmission Characteristics (Connectivity)

Mated Connection Table - Footnote:	* Up to Category 6A - TIA 568.C.2 when tested with Recommended CAT6A Cables.
Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max. Contact Resistance:	10 m-Ohm

Notes (Overall)

Notes: For additional information about this product, refer to Installation Guide PX106201, or visit our web at <http://www.belden.com>

Notes (Cont'd.): Suitable for Conductors with insulation OD range 0.033~0.042 in. (0.89~1.1 mm) and for Cable OD range 0.21~0.33 in. (5.5~8.5 mm).

Product Family

Part Number List:

Description	Part Number
CATEGORY 6A FIELD MOUNT PLUG 568A/B, UTP, SMALL	CAPFMUS-S1
CATEGORY 6A FIELD MOUNT PLUG 568A/B, UTP, LARGE	CAPFMUL-S1
CATEGORY 6A FIELD MOUNT PLUG 568A/B, SHIELDED, SMALL	CAPFMFS-S1
CATEGORY 6A FIELD MOUNT PLUG 568A/B, SHIELDED, LARGE	CAPFMFL-S1

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
CAPFMUS-S1	1 EA	0.028 KG			CAT6A FIELD PLUG T568A/B SMALL

Revision Number: 0 Revision Date: 10-12-2016

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.